# **Product datasheet**

Specifications





# Vigi iC60 - earth leakage add-on block - 4P - 25A - 30mA - AC type

A9V41425

#### Main

Range	Acti9	
Product Or Component Type	Add-on residual current devices	
Device Short Name	Vigi iC60	
Poles Description	4P	
[In] Rated Current	25 A	
Earth-Leakage Sensitivity	30 mA	
Earth-Leakage Protection Time Delay	2 Instantaneous	
Earth Leakage Protection Type	Type AC	
Network Type	AC	
Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	400415 V AC 50/60 Hz conforming to EN/IEC 61009-1 400415 V AC 50/60 Hz conforming to EN/IEC 61009-2-1	
Standards	EN/IEC 61009-1 EN/IEC 61009-2-1	
9 Mm Pitches	6	

## Complementary

Device Location In System	Outgoer	
Residual Current Tripping Technology	Voltage independent	
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-2	
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 Reflex iC60	
Product Compatibility	Single terminal	
Local Signalling	Trip indicator	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
Electrical Connection To Mcb	By screws	
Comb Busbar And Distribution Block Compatibility	Bottom: YES	
Height	91 mm	
Width	54 mm	
Depth	73.5 mm	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight	0.245 kg	
Connections - Terminals	Tunnel type terminal downside for 1 cable(s) 125 mm² rigid without cable end Tunnel type terminal downside for 1 cable(s) 116 mm² flexible without cable end Tunnel type terminal downside for 1 cable(s) 116 mm² flexible with cable end	
Wire Stripping Length	14 mm for bottom connection	
Tightening Torque	ening Torque 2 N.m bottom	

## **Environment**

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529	
Pollution Degree	3 conforming to IEC 60947-2	
Electromagnetic Compatibility	8/20 µs impulse withstand, 250 A conforming to IEC 61009-1	
Ambient Air Temperature For Operation	-560 °C	
Ambient Air Temperature For Storage	-4085 °C	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.700 cm
Package 1 Width	11.500 cm
Package 1 Length	14.100 cm
Package 1 Weight	215.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	15
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.730 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Plastic Parts Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information