Product datasheet

Specifications



Actassi - patch panel - category 6 -UTP - 24 Port - 1U - straight loaded

ACTPP6U24NSS_SE

Discontinued on: May 12, 2023

(!) Discontinued

Main

Range Of Product	Actassi	
Product Or Component Type	Patch panel	
Device Application	Communication	
Device Presentation	Loaded	
Provided Equipment	With RJ45 connectors Rear cable manager Front label holder 3 Cable fixing hardware Mounting hardware Retaining cap With shutter	
Colour Tint	Front plate blue glossy	
Colour Code	568 A/B	

Complementary

[In] Rated Current	1.5 A
	1.5 A
Rated Voltage	72 V DC
Dielectric Strength	1000 V for 1 min at 60 Hz
Contacts Material	Modular connector: phosphor bronze with 50 micro-inches gold over 100 micro- inches nickel IDC connector: phosphor bronze with nickel plating
Number Of Port	24 port of UTP
Product Compatibility	standard 19" cabinet/rack
Awg Gauge	AWG 24AWG 22
Cable Outer Diameter	0.91.22 mm
Communication Network Category	6
Contact Resistance	20 mOhm
Insulation Resistance	>= 200 MOhm
Minimum Number Of Matings	750 cycles
Number Of Rack Unit	1U
Plug, Socket, Control Station Shape	Straight
Surface Finish	Powder coated
Type Of Connector	S-110 keystone
Type Of Connector	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Ambient Air Temperature For Operation	-4070 °C
Ambient Air Temperature For Storage	-2060 °C
Relative Humidity	093 %
Flame Retardance	UL94-V0
Standards	ISO/IEC 11801 Ed.2, 2002 ANSI/TIA-568-C.2 IEC 60603-7
Product Certifications	UL listed ETL verified

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	13 cm
Package 1 Length	42 cm
Package 1 Weight	854 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	10
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	9890 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	150 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	89120 g

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations