Product datasheet

Specification

Main





! Discontinued - Service only

variable speed drive ATV312 - 15kW - 32kVA - 492 W - 380..500 V - 3-phase supply

ATV312HD15N4

- ! To be discontinued on: Sep 4, 2027
- To be end-of-service on: Sep 4, 2033

| Range Of Product | Altivar 312 |
|---------------------------------------|--|
| Product Or Component Type | Variable speed drive |
| Product Destination | Asynchronous motors |
| Product Specific Application | Simple machine |
| Assembly Style | With heat sink |
| Component Name | ATV312 |
| Motor Power Kw | 15 kW |
| Motor Power Hp | 20 hp |
| [Us] Rated Supply Voltage | 380500 V - 1510 % |
| Supply Frequency | 5060 Hz - 55 % |
| Network Number Of Phases | 3 phases |
| Line Current | 48.2 A at 380 V, Isc = 22 kA 36.8 A at 500 V |
| Emc Filter | Integrated |
| Apparent Power | 32 kVA |
| Maximum Transient Current | 49.5 A for 60 s |
| Power Dissipation In W | 492 W at nominal load |
| Speed Range | 150 |
| Asynchronous Motor Control Profile | Sensorless flux vector control with PWM type motor control signal Factory set : constant torque |
| Electrical Connection | Al1, Al2, Al3, AOV, AOC, R1A, R1B, R1C, R2A, R2B, Ll1Ll6 terminal 2.5 mm² AWG 14 L1, L2, L3, U, V, W, PA, PB, PA/+, PC/- terminal 25 mm² AWG 3 |
| Supply | Internal supply for logic inputs: 1930 V 100 mA, protection type: overload and short-circuit protection Internal supply for reference potentiometer (2.2 to 10 kOhm): 1010.8 V 10 mA, protection type: overload and short-circuit protection |
| Communication Port Protocol | Modbus CANopen |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

IP20 on upper part without cover plate IP21 on connection terminals IP31 on upper part IP41 on upper part



Ip Degree Of Protection

| Option Card | Communication card for CANopen daisy chain |
|-------------|--|
| | Communication card for DeviceNet |
| | Communication card for Fipio |
| | Communication card for Modbus TCP |
| | Communication card for Profibus DP |

Complementary

| Complementary | |
|-----------------------------|---|
| Supply Voltage Limits | 323550 V |
| Prospective Line Isc | 22 kA |
| Continuous Output Current | 33 A at 4 kHz |
| Output Frequency | 0500 Hz |
| Nominal Switching Frequency | 4 kHz |
| Switching Frequency | 216 kHz adjustable |
| Transient Overtorque | 170200 % of nominal motor torque |
| Braking Torque | 150 % during 60 s with braking resistor 100 % with braking resistor continuously 150 % without braking resistor |
| Regulation Loop | Frequency PI regulator |
| Motor Slip Compensation | Adjustable Automatic whatever the load Suppressable |
| Output Voltage | <= power supply voltage |
| Tightening Torque | Al1, Al2, Al3, AOV, AOC, R1A, R1B, R1C, R2A, R2B, Ll1Ll6: 0.6 N.m L1, L2, L3, U, V, W, PA, PB, PA/+, PC/-: 4.5 N.m |
| Insulation | Electrical between power and control |
| Analogue Input Number | 3 |
| Analogue Input Type | Al1 configurable voltage 010 V, input voltage 30 V max, impedance: 30000 Ohm Al2 configurable voltage +/- 10 V, input voltage 30 V max, impedance: 30000 Ohm Al3 configurable current 020 mA, impedance: 250 Ohm |
| Sampling Duration | Al1, Al2, Al3: 8 ms analog Ll1Ll6: 4 ms discrete |
| Response Time | AOV, AOC 8 ms for analog R1A, R1B, R1C, R2A, R2B 8 ms for discrete |
| Linearity Error | +/- 0.2 % for output |
| Analogue Output Number | 1 |
| Analogue Output Type | AOC configurable current: 020 mA, impedance: 800 Ohm, resolution: 8 bits AOV configurable voltage: 010 V, impedance: 470 Ohm, resolution: 8 bits |
| Discrete Input Logic | Logic input not wired (LI1LI4), < 13 V (state 1) Negative logic (source) (LI1LI6), > 19 V (state 0) Positive logic (source) (LI1LI6), < 5 V (state 0), > 11 V (state 1) |
| Discrete Output Number | 2 |
| Discrete Output Type | Configurable relay logic: (R1A, R1B, R1C) 1 NO + 1 NC - 100000 cycles Configurable relay logic: (R2A, R2B) NC - 100000 cycles |
| Minimum Switching Current | R1-R2 10 mA at 5 V DC |
| Maximum Switching Current | R1-R2: 2 A at 250 V AC inductive load, cos phi = 0.4 and L/R = 7 ms R1-R2: 2 A at 30 V DC inductive load, cos phi = 0.4 and L/R = 7 ms R1-R2: 5 A at 250 V AC resistive load, cos phi = 1 and L/R = 0 ms R1-R2: 5 A at 30 V DC resistive load, cos phi = 1 and L/R = 0 ms |
| Discrete Input Number | 6 |
| Discrete Input Type | (LI1LI6) programmable at 24 V, 0100 mA for PLC, impedance: 3500 Ohm |

| Acceleration And Deceleration Ramps | S, U or customized Linear adjustable separately from 0.1 to 999.9 s |
|-------------------------------------|--|
| Braking To Standstill | By DC injection |
| Protection Type | Input phase breaks: drive Line supply overvoltage and undervoltage safety circuits: drive Line supply phase loss safety function, for three phases supply: drive Motor phase breaks: drive Overcurrent between output phases and earth (on power up only): drive Overheating protection: drive Short-circuit between motor phases: drive Thermal protection: motor |
| Insulation Resistance | >= 500 mOhm 500 V DC for 1 minute |
| Local Signalling | 1 LED (red) for drive voltage Four 7-segment display units for CANopen bus status |
| Time Constant | 5 ms for reference change |
| Frequency Resolution | Analog input: 0.1100 Hz Display unit: 0.1 Hz |
| Connector Type | 1 RJ45 for Modbus/CANopen |
| Physical Interface | RS485 multidrop serial link |
| Transmission Frame | RTU |
| Transmission Rate | 10, 20, 50, 125, 250, 500 kbps or 1 Mbps for CANopen 4800, 9600 or 19200 bps for Modbus |
| Number Of Addresses | 1127 for CANopen 1247 for Modbus |
| Number Of Drive | 127 for CANopen 31 for Modbus |
| Marking | CE |
| Operating Position | Vertical +/- 10 degree |
| Outer Dimension | 390 x 245 x 190 mm 595 x 234 x 268 mm 330 x 245 x 190 mm |
| Height | 329.5 mm |
| Width | 245 mm |
| Depth | 192 mm |
| Net Weight | 11 kg |

Environment

| Dielectric Strength | 2410 V DC between earth and power terminals 3400 V AC between control and power terminals |
|-------------------------------|--|
| Electromagnetic Compatibility | 1.2/50 µs - 8/20 µs surge immunity test level 3 conforming to IEC 61000-4-5 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3 |
| Standards | IEC 61800-5-1 IEC 61800-3 |
| Product Certifications | UL CSA DNV GOST C-Tick NOM |
| Pollution Degree | 2 |
| Protective Treatment | TC |

| Vibration Resistance | 1 gn (f= 13150 Hz) conforming to EN/IEC 60068-2-6 1.5 mm (f= 313 Hz) conforming to EN/IEC 60068-2-6 |
|--|--|
| Shock Resistance | 15 gn for 11 ms conforming to EN/IEC 60068-2-27 |
| Relative Humidity | 595 % without condensation conforming to IEC 60068-2-3 595 % without dripping water conforming to IEC 60068-2-3 |
| Ambient Air Temperature For Storage | -2570 °C |
| Ambient Air Temperature For Operation | -1050 °C without derating (with protective cover on top of the drive) -1060 °C with derating factor (without protective cover on top of the drive) |
| Operating Altitude | <= 1000 m without derating 10003000 m with current derating 1 % per 100 m |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 28.0 cm |
| Package 1 Width | 29.0 cm |
| Package 1 Length | 40.0 cm |
| Package 1 Weight | 11.856 kg |
| Unit Type Of Package 2 | P06 |
| Number Of Units In Package 2 | 4 |
| Package 2 Height | 80.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 59.82 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
|-----------------------|---|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |