



Acti 9 Vertical TPN 18way with 3P NSX 250A incomer provision

A9HV318XNSX250

Main

Range	Acti9 Disbo
Product Name	Acti9 Vertical TPN
Product Or Component Type	Distribution board
Device Application	Low voltage electrical distribution
Enclosure Type	Standard
Door Type	Flat
Provided Equipment	enclosure pan assembly earth terminal block neutral terminal block
Colour	White (RAL 9003)

Complementary

[le] Rated Operational Current	250 A
[Icw] Rated Short-Time Withstand Current	25 kA for 0.3 s
[lpk] Rated Peak Withstand Current	52.5 kA
Enclosure Mounting	Flush
Incomer Device	3P MCCB
Number Of Ways	18 ways
Enclosure Material	Powder coated sheet steel
Height	685 mm
Width	425 mm
Depth	148 mm
Ip Degree Of Protection	IP41
Targeted Country	Egypt

Environment

Standards	IEC 61439-3
Ambient Air Temperature For Operation	-550 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	14.0 cm	
Package 1 Width	42.5 cm	
Package 1 Length	71.5 cm	
Package 1 Weight	13.4 kg	_



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations