Product datasheet

Specification

Main





integrated drive ILS with stepper motor - 24..36 V - Profibus DP - 3.5 A

ILS1B571PB1A0

! To be discontinued on: Sep 4, 2027

! To be end-of-service on: Sep 4, 2033

Range Of Product	Lexium integrated drive
Product Or Component Type	Motion integrated drive
Device Short Name	ILS
Motor Type	3-phase stepper motor
Number Of Motor Poles	6
Network Number Of Phases	Single phase
[Us] Rated Supply Voltage	24 V
[co]ou cupp.y volgo	36 V
Network Type	DC
Communication Interface	Profibus DP, integrated
Length	101.9 mm
Winding Type	Medium speed of rotation and medium torque
Electrical Connection	Printed circuit board connector
Holding Brake	Without
Gear Box Type	Without
Nominal Speed	1000 rpm at 36 V
•	500 rpm at 24 V
	·
Nominal Torque	0.45 N.m
Holding Torque	0.51 N.m

Complementary

Transmission Rate	9.6, 19.2, 45.45, 93.75, 187.5, 500, 1500, 3000, 6000 and 12000 kbauds
Mounting Support	Flange
Motor Flange Size	57 mm
Number Of Motor Stacks	1
Centring Collar Diameter	38.1 mm
Centring Collar Depth	1.6 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	5.2 mm
Circle Diameter Of The Mounting Holes	66.6 mm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Foodbook Tuno	Tester codes
Feedback Type	Index pulse
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	6.35 mm
Shaft Length	21 mm
Supply Voltage Limits	1840 V
Current Consumption	3500 mA maximum
Associated Fuse Rating	10 A
Input/Output Type	4 signals (each be used as input or output)
Voltage State 0 Guaranteed	-34.5 V
Voltage State 1 Guaranteed	1530 V
Discrete Input Current	10 mA at 24 V on/STO_A for safety input 3 mA at 24 V on/STO_B for safety input 2 mA at 24 V for 24 V signal interface
Discrete Output Voltage	2325 V
Maximum Switching Current	100 mA per output 200 mA total
Protection Type	Short circuit of the output voltage Overload of output voltage Safe torque off
Peak Stall Torque	0.45 N.m
Continuous Stall Torque	0.45 N.m
Speed Feedback Resolution	20000 points/turn
Accuracy Error	+/- 6 arc min
Rotor Inertia	0.1 kg.cm ²
Maximum Mechanical Speed	3000 rpm
Maximum Radial Force Fr	24 N
Maximum Axial Force Fa	100 N (tensile force) 8.4 N (force pressure)
Service Life In Hours	20000 h bearing
Marking	CE
Type Of Cooling	Natural convection
Net Weight	1.3 kg

Environment

Standards	EN/IEC 61800-3 IEC 60072-1 EN 61800-3:2001, second environment IEC 61800-3, Ed 2 EN 50347 EN/IEC 50178 EN 61800-3: 2001-02	
Product Certifications	TÜV cUL UL	
Ambient Air Temperature For Operation	5065 °C (with power derating of 2 % per °C) 050 °C (without derating)	
Permissible Ambient Air Temperature Around The Device	105 °C power amplifier 110 °C motor	

Ambient Air Temperature For Storage	-2570 °C
Operating Altitude	<= 1000 m without derating
Relative Humidity	1585 % without condensation
Vibration Resistance	20 m/s² (f= 10500 Hz) 10 cycles conforming to EN/IEC 60068-2-6
Shock Resistance	150 m/s² 1000 shocks conforming to EN/IEC 60068-2-29
Ip Degree Of Protection	IP41 shaft bushing: conforming to EN/IEC 60034-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	17 cm
Package 1 Length	24 cm
Package 1 Weight	1.494 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	13.204 kg
Package 3 Height	30.0 cm

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes
Pvc Free	


Certifications & Standards

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Reach Regulation	REACh Declaration

Dimensions Drawings

Integrated Drive


Dimensions



- 1 Accessories: I/O signal insert with industrial connectors
- 2 Option: industrial connectors
- 3 Earth (ground) terminal
- 4 Accessories: cable entries $\emptyset = 3 \dots 9 \text{ mm}/0.12 \dots 0.35 \text{ in.}$
- L 101.9 mm/4.01 in.
- D 6.35 mm/0.25 in.

Connections and Schema

Connection Example with 4 I/O Signals




Product datasheet

ILS1B571PB1A0

Performance Curves

Torque Characteristics



- X Speed of rotation in rpm
- Y Torque in Nm
- 1.1 Max. torque at 24 V
- 1.2 Max. torque at 36 V