Product datasheet

Specification





TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 150 A - 115 V AC 50/60 Hz coil

LC1D150FE7

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-4 AC-1 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 1000 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	200 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 150 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 150 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	115 V AC 50/60 Hz

Complementary

Motor Power Kw	40 kW at 220230 V AC 50/60 Hz (AC-3)		
	75 kW at 380400 V AC 50/60 Hz (AC-3)	75 kW at 380400 V AC 50/60 Hz (AC-3)	
	80 kW at 415440 V AC 50/60 Hz (AC-3)		
	90 kW at 500 V AC 50/60 Hz (AC-3)		
	100 kW at 660690 V AC 50/60 Hz (AC-3)		
	75 kW at 1000 V AC 50/60 Hz (AC-3)		
	22 kW at 400 V AC 50/60 Hz (AC-4)		
	40 kW at 220230 V AC 50/60 Hz (AC-3e)		
	75 kW at 380400 V AC 50/60 Hz (AC-3e)		
	80 kW at 415440 V AC 50/60 Hz (AC-3e)		
	90 kW at 500 V AC 50/60 Hz (AC-3e)		
	100 kW at 660690 V AC 50/60 Hz (AC-3e)		
	75 kW at 1000 V AC 50/60 Hz (AC-3e)		
Motor Power Hp	40 hp at 200/208 V AC 50/60 Hz for 3 phases motors		
	50 hp at 230/240 V AC 50/60 Hz for 3 phases motors		
	100 hp at 460/480 V AC 50/60 Hz for 3 phases motors		
	125 hp at 575/600 V AC 50/60 Hz for 3 phases motors		
Compatibility Code	LC1D		
Pole Contact Composition	3 NO		
Protective Cover	With		
[Ith] Conventional Free Air Thermal Current			
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1		
	250 A DC for signalling circuit conforming to IEC 60947-5-1		
	1660 A at 440 V for power circuit conforming to IEC 60947		
	3 · · · · · · · · · · · · · · · · · · ·		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Rated Breaking Capacity	1400 A at 440 V for power circuit conforming to IEC 60947
[lcw] Rated Short-Time Withstand Current	250 A 40 °C - 10 min for power circuit 580 A 40 °C - 1 min for power circuit 1200 A 40 °C - 10 s for power circuit 1400 A 40 °C - 1 s for power circuit 1400 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 315 A gG at <= 690 V coordination type 1 for power circuit 250 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.6 mOhm - Ith 200 A 50 Hz for power circuit
Power Dissipation Per Pole	24 W AC-1 13.5 W AC-3 13.5 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Power circuit: 1000 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947
Safety Reliability Level	B10d = 684932 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 10000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	8 Mcycles
Electrical Durability	0.85 Mcycles 150 A AC-3 at Ue <= 440 V 1 Mcycles 200 A AC-1 at Ue <= 440 V 0.85 Mcycles 150 A AC-3e at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz standard
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.30.5 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.15 Uc (-4055 °C):operational AC 50/60 Hz 11.15 Uc (5570 °C):operational AC 50/60 Hz
Inrush Power In Va	280350 VA 60 Hz cos phi 0.9 (at 20 °C) 280350 VA 50 Hz cos phi 0.9 (at 20 °C)
Hold-In Power Consumption In Va	218 VA 60 Hz cos phi 0.9 (at 20 °C) 218 VA 50 Hz cos phi 0.9 (at 20 °C)
Heat Dissipation	34.5 W at 50/60 Hz
Operating Time	2035 ms closing 4075 ms opening
Maximum Operating Rate	1200 cyc/h 60 °C

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with	
	cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: flexible with	
	cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: flexible without	
	cable end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible without	
	cable end Control circuit: screw clamp terminals 1 12.5 mm² - cable stiffness: solid without	
	cable end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: solid without	
	cable end Power circuit: connector 1 10120 mm² - cable stiffness: flexible without cable end	
	Power circuit: connector 2 1050 mm² - cable stiffness: flexible without cable end	
	Power circuit: connector 1 10120 mm² - cable stiffness: flexible with cable end	
	Power circuit: connector 2 1050 mm² - cable stiffness: flexible with cable end Power circuit: connector 1 10120 mm² - cable stiffness: solid without cable end	
	Power circuit: connector 2 1050 mm² - cable stiffness: solid without cable end	
Tightening Torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm	
	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 12 N.m - on connector hexagonal screw head 4 mm	
	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver pozidriv No 2	
Auxiliary Contact Composition	1 NO + 1 NC	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1	
Signalling Circuit Frequency	type mirror contact 1 NC conforming to IEC 60947-4-1 25400 Hz	
Minimum Switching Voltage		
Minimum Switching Current	17 V for signalling circuit	
Insulation Resistance	5 mA for signalling circuit > 10 MOhm for signalling circuit	
Non-Overlap Time		
	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	
	1 late	
Environment		
Standards	CSA C22.2 No 14	
	EN 60947-4-1	
	EN 60947-5-1	
	IEC 60947-4-1 IEC 60947-5-1	
	UL 508	
Product Certifications	LROS (Lloyds register of shipping) GOST	
	UL	
	DNV	
	CSA GL	
	CCC	
	BV	
	RINA	
	UKCA CE	
Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Protective Treatment	TH conforming to IEC 60068-2-30	
Climatic Withstand	conforming to IACS E10 exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	

V1 conforming to UL 94

Flame Retardance

Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (6 Gn for 11 ms)
Height	158 mm
Width	120 mm
Depth	136 mm
Net Weight	2.5 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.500 cm
Package 1 Width	17.500 cm
Package 1 Length	21.000 cm
Package 1 Weight	2.475 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	27
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	81.742 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
⊘	Pvc Free	


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

LC1D150FE7

Dimensions Drawings

Dimensions



(1) Minimum electrical clearance

LC1		D115 and D150 (3-pole)
а		120
	with LA4 DA2	174
b1	with LA4 DF, DT	185
ы	with LA4 DM, DL	188
	with LA4 DW	188
	without cover or add-on blocks	132
С	with cover, without add-on blocks	136
с1	with LAD N or C (2 or 4 contacts)	150
c2	with LA6 DK20	155
с3	with LAD T, R, S	168
C3	with LAD T, R, S and sealing cover	172

Connections and Schema

Wiring

