Product datasheet

Specifications





Contactor,Easy TeSys Control,LC1E, 3P(3NO),AC-3,<=440V,300A,220V AC coil,50Hz

LC1E300M5

Main

Range	Easy TeSys	
Range Of Product	Easy TeSys Control	
Product Or Component Type	Contactor	
Device Short Name	LC1E	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-1 AC-3	
Poles Description	3P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 50/60 Hz	
[le] Rated Operational Current	300 A (at <55 °C) at <= 440 V AC AC-3 for power circuit 320 A (at <40 °C) at <= 440 V AC AC-1 for power circuit	
[Uc] Control Circuit Voltage	220 V AC 50 Hz	

Complementary

Motor Power Kw	90 kW at 220230 V AC 50/60 Hz (AC-3)
	160 kW at 380400 V AC 50/60 Hz (AC-3)
	160 kW at 415 V AC 50/60 Hz (AC-3)
	185 kW at 440 V AC 50/60 Hz (AC-3)
	200 kW at 500 V AC 50/60 Hz (AC-3)
	250 kW at 660690 V AC 50/60 Hz (AC-3)
Pole Contact Composition	3 NO
[Ith] Conventional Free Air Thermal Current	320 A (at 40 °C)
Thermal Current	
Irms Rated Making Capacity	3000 A at 440 V AC for power circuit conforming to IEC 60947-4-1
Rated Breaking Capacity	2400 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	2200 A 40 °C - 10 s for power circuit
Associated Fuse Rating	10 A gG at <= 690 V coordination type 1 for control circuit conforming to IEC
	60947-5-1
	500 A gG at <= 690 V coordination type 1 for power circuit
Average Impedance	0.3 mOhm - Ith 320 A 50 Hz for power circuit
Power Dissipation Per Pole	27 W AC-3
	31 W AC-1
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
Overvoltage Category	Ш
Pollution Degree	3
[Limp] Botod Impulso Withstand	0 b) and compared to the neuron size of contracts to IEC CO047

[Uimp] Rated Impulse Withstand 8 kV coil not connected to the power circuit conforming to IEC 60947 Voltage

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Mechanical Durability	5000000 cycles
Electrical Durability	400000 cycles AC-1 500000 cycles AC-3
Control Circuit Type	AC at 50 Hz
Control Circuit Voltage Limits	0.851.1 Uc (-555 °C):operational 50 Hz 0.350.55 Uc (-555 °C):drop-out 50 Hz
Inrush Power In Va	650 VA 50 Hz cos phi 0.9 (at 20 °C) 650 VA 60 Hz cos phi 0.9 (at 20 °C)
Hold-In Power Consumption In Va	10 VA 50 Hz cos phi 0.9 (at 20 °C) 10 VA 60 Hz cos phi 0.9 (at 20 °C)
Heat Dissipation	8 W for control circuit
Operating Time	4065 ms on closing 100170 ms on opening
Maximum Operating Rate	1200 cyc/h 55 °C
Connections - Terminals	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 12.5 mm ² - cable stiffness: flexible with cable end Power circuit: cable with lug - external diameter: 240 mm Power circuit: bars 2 - busbar cross section: 5 x 30 mm
Tightening Torque	Control circuit: 1.2 N.m Power circuit: 35 N.m
Minimum Switching Voltage	17 V for control circuit
Minimum Switching Current	5 mA for control circuit
Insulation Resistance	> 10 MOhm for control circuit
Non-Overlap Time	1.5 ms on energisation guaranteed between NC and NO contact1.5 ms on de-energisation guaranteed between NC and NO contact
Mounting Support	Plate

Environment

Standards	IEC 60947-1 IEC 60947-4-1 IEC 60947-5-1	
Product Certifications	EAC CE	
Ip Degree Of Protection	IP00 conforming to IEC 60529	
Permissible Ambient Air Temperature Around The Device	-2070 °C at Uc -6080 °C storage -555 °C operation	
Operating Altitude	3000 m without derating	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Mechanical Robustness	Vibrations contactor open (1.5 Gn, 5300 Hz) Vibrations contactor closed (3 Gn, 5300 Hz) Shocks contactor open (6 Gn for 11 ms) Shocks contactor closed (7 Gn for 11 ms)	
Height	206 mm	
Width	213 mm	

Depth	219 mm
Net Weight	8.5 kg

Packing Units

0	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	27.0 cm
Package 1 Width	25.0 cm
Package 1 Length	31.0 cm
Package 1 Weight	9.446 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information