Product datasheet

Specification





TeSys K contactor - 3P - AC-3 <= 440 V 16 A - 1 NC aux. - 48 V AC coil

LC1K1601E7

Main

Range	TeSys
Product Or Component Type	Contactor
Device Short Name	LC1K
Device Application	Control
Contactor Application	Motor control

Complementary

· · · · · · · · · · · · · · · · · ·	
Utilisation Category	AC-3
	AC-3e
Poles Description	3P
- Description	Jr
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC <= 400 Hz
	Signalling circuit: <= 690 V AC <= 400 Hz
[le] Rated Operational Current	16 A (at <60 °C) at <= 440 V AC AC-3 for power circuit
	16 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz
Motor Power Kw	4 kW at 220230 V AC 50/60 Hz AC-3
	7.5 kW at 380415 V AC 50/60 Hz AC-3
	5.5 kW at 440 V AC 50/60 Hz AC-3
	4 kW at 690 V AC 50/60 Hz AC-3
	4 kW at 220230 V AC 50/60 Hz AC-3e
	7.5 kW at 380415 V AC 50/60 Hz AC-3e
	5.5 kW at 440 V AC 50/60 Hz AC-3e
	4 kW at 690 V AC 50/60 Hz AC-3e
Auxiliary Contact Composition	1 NC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air	20 A (at 60 °C) for power circuit
Thermal Current	10 A (at 50 °C) for signalling circuit
Irms Rated Making Capacity	160 A AC for power circuit conforming to IEC 60947
	110 A AC for signalling circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 440 V conforming to IEC 60947
	80 A at 500 V conforming to IEC 60947
	70 A at 660690 V conforming to IEC 60947

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Icw] Rated Short-Time Withstand	115 A 50 °C - 1 s for power circuit
Current	105 A 50 °C - 5 s for power circuit
	100 A 50 °C - 10 s for power circuit
	75 A 50 °C - 30 s for power circuit
	55 A 50 °C - 1 min for power circuit
	50 A 50 °C - 3 min for power circuit
	25 A 50 °C - >= 15 min for power circuit
	80 A - 1 s for signalling circuit
	90 A - 500 ms for signalling circuit
	110 A - 100 ms for signalling circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit
-	25 A aM for power circuit
	10 A gG for signalling circuit conforming to IEC 60947
	10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
[Hi] Poted Insulation Voltage	Device size it COO V conforming to III 500
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to UL 508
	Power circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-5-1
	Signalling circuit: 600 V conforming to UL 508
	Power circuit: 600 V conforming to CSA C22.2 No 14
	Signalling circuit: 600 V conforming to CSA C22.2 No 14
Insulation Resistance	> 10 MOhm for signalling circuit
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4.5 VA (at 20 °C)
Heat Dissipation	1.3 W
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <50 °C) Drop-out: >= 0.20 Uc (at <50 °C)
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid
	Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end
	Screw clamp terminals 2 cable(s) 1.54 mm²solid
	Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end
Maximum Operating Rate	3600 cyc/h
Auxiliary Contacts Type	tura instantanagua 1 NC
Auxiliary Contacts Type	type instantaneous 1 NC
Signalling Circuit Frequency	<= 400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Mounting Support	Plate
	Rail
Tightening Torque	0.81.3 N.m - on screw clamp terminals Philips No 2
	0.81.3 N.m - on screw clamp terminals flat Ø 6 mm
	0.81.3 N.m - on screw clamp terminals pozidriv No 2
On a notion or Time a	40.00 7.1
Operating Time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
and the second	
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Non Overlap Distance	0.5 mm
Mechanical Durability	
	10 Mcycles
Electrical Durability	1.3 Mcycles 16 A AC-3 at Ue <= 440 V 1.3 Mcycles 16 A AC-3e at Ue <= 440 V

Mechanical Robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5300 Hz conforming to IEC 60068-2-6
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.18 kg

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Ip Degree Of Protection	IP2X conforming to VDE 0106
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ambient Air Temperature For Operation	-2550 °C
Ambient Air Temperature For Storage	-5080 °C
Operating Altitude	2000 m without derating
Flame Retardance	V1 conforming to UL 94

Packing Units

racking office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	6.000 cm
Package 1 Length	6.500 cm
Package 1 Weight	180.500 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.285 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	800
Package 3 Height	75.000 cm

Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	156 560 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information