Product datasheet

Specifications





control relay, TeSys K, 4P(2NO+2NC), 690V, 230V AC coil, without integral suppression device

CA2KN223P7

Main

Range	TeSys
Product Name	TeSys CAK
Product Or Component Type	Control relay
Device Short Name	CA2K
Contactor Application	Control circuit
Utilisation Category	AC-15 DC-13
Pole Contact Composition	2 NO + 2 NC
[Ue] Rated Operational Voltage	<= 690 V <= 400 Hz
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz

Complementary

oomprementary	
[Ith] Conventional Free Air Thermal Current	10 A (at 50 °C)
Irms Rated Making Capacity	110 A conforming to IEC 60947
Associated Fuse Rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C 690 V conforming to BS 5424 600 V conforming to CSA C22.2 No 14
Mounting Support	Plate Rail
Connections - Terminals	Spring terminals 1 cable(s) 0.751.5 mm ² solid Spring terminals 1 cable(s) 0.751.5 mm ² flexible without cable end
Control Circuit Voltage Limits	Drop-out: 0.20.75 Uc (at <50 °C) Operational: 0.81.15 Uc (at <50 °C)
Operating Time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing 1525 ms coil de-energisation and NC closing 515 ms coil energisation and NC opening
Mechanical Durability	10 Mcycles
Maximum Operating Rate	10000 cyc/h
Immunity To Microbreaks	2 ms
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4 5 \/A (at 20 °C)

Hold-In Power Consumption In Va 4.5 VA (at 20 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Heat Dissipation	1.3 W
Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA
Non Overlap Distance	0.5 mm
Insulation Resistance	> 10 MOhm
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.18 kg

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1	
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA	
Protective Treatment	TC conforming to IEC 60068	
Ambient Air Temperature For Operation	-2550 °C	
Ambient Air Temperature For Storage	-5080 °C	
Operating Altitude	2000 m without derating	
Flame Retardance	Retardance V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102	
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Shocks contactor open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed: 15 Gn for 11 ms conforming to IEC 60068-2-27	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	5.800 cm
Package 1 Length	6.400 cm
Package 1 Weight	183.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.655 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information