

Product datasheet

Specifications



ARGUS standard outdoor 360° - blister

CCTR1P008

Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Movement detector
Load type	Incandescent lamp: 1000 W, AC Low voltage halogen lamp with wire-wound transformer: 500 VA Low voltage halogen lamp with electronic transformer: 315 VA Fluorescent tube: 250 VA, AC Compact fluorescent lamp: 4 x 23 W, AC Capacitive: : 6 A, 28 µF, AC Capacitive: : 10 A, 21 µF, AC Halogen lamp: 800 W, AC
Colour tint	White
Type of packing	Blister

Complementary

[Ue] rated operational voltage	220...240 V
Network frequency	50 Hz 220...240 V
Output current	10 A
Type of setting	Time adjustment Light sensitivity adjustable
Time delay	5 s...20 min
Light intensity adjustment	5...2000 lux
Horizontal detection angle	0...360 °
Detection range	Frontal: 12 m
Material	PC (polycarbonate) matt
Device mounting	Surface
Mounting height	2.5 m

Environment

IP degree of protection	IP55
Ambient air temperature for operation	-15...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	18.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	280.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	4.258 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)