

Product datasheet

Specifications



EBE - EnOcean 868MHz - Puck Blind control 2gng module

LSS10020063

 **Discontinued on:** Sep 30, 2023

 **Discontinued**

Main

Range	EcoStruxure Building Expert
Product Name	EnOcean
Product Or Component Type	Remote receiver module
Device Presentation	Flush-mounting module

Complementary

[Ue] Rated Operational Voltage	230 V AC 50 Hz
Transmission Frequency	868.3 MHz
Number Of Inputs	32
Load Type	Inductive 600 VA
Switch Application	Roller blind
Switch Function	Roller blind
Wiring Configuration	2-wire
Connections - Terminals	5-position plug-in connector 1.5 mm² rigid
Protection Type	10 A circuit breaker protection
Fixing Mode	By screws: back box
Ip Degree Of Protection	IP20
Device Mounting	Flush
Quantity Per Set	Set of 1

Environment

Ambient Air Temperature For Operation	-10...45 °C
Ambient Air Temperature For Storage	-40...85 °C
Marking	CE
Standards	IEC 60669-2-1
Directives	1999/5/EC - R&TTE directive

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.6 cm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	6.4 cm
Package 1 Length	8.9 cm
Package 1 Weight	65.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div><div>✓</div><div>Rohs Exemption Information</div></div><div>Yes</div></div>	
<div><div><div>Eu Rohs Directive</div><div>Compliant</div><div>EU RoHS Declaration</div></div></div>	
<div><div><div>China Rohs Regulation</div><div>China RoHS declaration</div></div></div>	