# **Product datasheet**

Specifications





### Circuit breaker, ComPact NSX100R, 200kA/415VAC, MicroLogic 2.2M trip unit 100A, 3 poles 3d

LV433276

- () Discontinued on: Sep 4, 2023
- () To be end-of-service on: Sep 3, 2026

#### Main

Man	
Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100250
Device Short Name	NSX100R
Product Or Component Type	Circuit breaker
Device Application	Motor
Number Of Poles	3P
Protected Poles Description	3t
[In] Rated Current	100 A at 65 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	200 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 80 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 45 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	R 200 kA 415 V AC
Trip Unit Name	MicroLogic 2.2 M
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LSol
Control Type	Toggle
Circuit Breaker Mounting Mode	Fixed

### Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Ics] Rated Service Short-Circuit Breaking Capacity	200 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 200 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 200 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 80 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 45 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	50000 cycles
Electrical Durability	10000 cycles at 690 V In 20000 cycles at 690 V In/2 30000 cycles at 440 V In 50000 cycles at 440 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
Trip Unit Rating	100 A at 65 °C
Motor Tripping Class	5 20 10
Complementary Motor Protection	Phase unbalance
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	50100 A
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	10 s at 7.2 x lr for trip class 10 120 s at 1.5 x lr for trip class 5 20 s at 7.2 x lr for trip class 20 240 s at 1.5 x lr for trip class 10 26 s at 6 x lr for trip class 20 480 s at 1.5 x lr for trip class 20 5 s at 7.2 x lr for trip class 5 13.5 s at 6 x lr for trip class 10 6.5 s at 6 x lr for trip class 5
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick- Up Adjustment Range	513 x lr
Short-Time Protection Delay Adjustment Type Tsd	Fixed
Instantaneous Protection Pick-Up Adjustment Type li	Fixed
[li] Instantaneous Protection Pick- Up Adjustment Range	1500 A
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Number Of Slots For Electrical Auxiliaries	5 slot(s)
Local Signalling	Flashing LED (green) for ready to operate LED 95 % Ith (red) for temperature over set point
Width (W)	105 mm
Height (H)	161 mm
Depth (D)	86 mm

Net Weight

### Environment

Standards	EN/IEC 60947
Product Certifications	EAC CCC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	13.5 cm
Package 1 Length	19.2 cm
Package 1 Weight	1.939 kg

#### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information