

Product datasheet

Specifications



VIGILOHM IM10-H 110 - 230 VAC

IMD-IM10-H

Main

Range	Vigilohm
Device Short Name	IM10-H
Product Or Component Type	Insulation monitoring device
Device Application	Hospital
Earthing System	IT
Language	Italian Spanish Chinese Russian English Portuguese German French

Complementary

Network Rated Voltage	0...230 V - AC at 50/60 Hz (phase to neutral) 0...100 V - DC
Type Of Measurement	Network insulation resistance - measurement range: 1 kOhm...10 MOhm
Local Signalling	Green indicator light: satisfactory insulation resistance Orange indicator light: below fault threshold
Threshold Setting	Fault: 50...500 kOhm
Response Time	<= 1 s
Auxiliary Supply Voltage	125...250 V DC +/- 15 % 110...230 V AC 50/60 Hz +/- 15 %
Power Consumption In Va	12 VA
Measurement Voltage	25 V
Measurement Current	0...0.2 mA
Internal Impedance	110 kOhm - AC at 50/60 Hz
Test Function	Manual
Output Contact	1 C/O standard or fail-safe
Breaking Capacity	250 V - AC at 6 A 12...24 V - DC at 6 A
Communication Port Protocol	-
Display Type	Digital display
Mounting Mode	Flush-mounted Clip-on
Mounting Support	Panel DIN rail

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Removable screw terminal block0.2...2.5 mm²
Material	Thermoplastic
Net Weight	0.25 kg
Height	110 mm
Width	96 mm
Depth	59 mm

Environment

Dielectric Strength	4000 V - AC 5500 V - DC
Ip Degree Of Protection	Front face: IP52
Environmental Characteristic	Exposure to damp heat not in service conforming to IEC 60068-2-30 Exposure to damp heat in service conforming to IEC 60068-2-56 Salt mist conforming to IEC 60068-2-52
Pollution Degree	2
Type Of Installation	Indoor
Standards	IEC 61010-1 IEC 61557-8 IEC 60364-7-710 IEC 61326-2-4
Product Certifications	EAC BV CE DNV
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	13.5 cm
Package 1 Length	16.5 cm
Package 1 Weight	426 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.075 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins