


# Product datasheet

Specifications



Plain cable gland plate, PanelSeT SFN, Spacial SF, for electrical enclosure W800 D400mm, fixed by clips

NSYEC84

## Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial SF Spacial Spacial SFM
Mounting Location	Enclosure bottom
Cable Gland Type	Standard
Cable Entry	Plain
Device Composition	fixing elements 1 plate
Quantity Per Set	Set of 1
Material	Galvanised steel

## Complementary

Height	25 mm
Width	Nominal: 800 mm Useful: 616 mm Real: 655 mm
Depth	400 mm nominal:
Thickness	1.5 mm

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	31.5 cm
Package 1 Length	65.0 cm
Package 1 Weight	2.842 kg

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations