Specifications





Interface plug-in relay, 16 A, 1 CO, 230 V AC

RSB1A160P7

Main

Range Of Product	Harmony Electromechanical Relays
Series Name	Interface relay
Product Or Component Type	Plug-in relay
Device Short Name	RSB
Contacts Type And Composition	1 C/O
Contact Operation	Standard
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz
[Ithe] Conventional Enclosed Thermal Current	16 A at -4040 °C
Status Led	Without
Control Type	Without push-button

Complementary

e emprementar y		
Shape Of Pin	Flat (PCB type)	
Average Coil Resistance	33000 Ohm network: AC at 20 °C +/- 10 %	
[Ue] Rated Operational Voltage	184345 V AC 50/60 Hz	
[Ui] Rated Insulation Voltage	400 V conforming to IEC 60947	
[Uimp] Rated Impulse Withstand Voltage	3.6 kV conforming to IEC 61000-4-5	
Contacts Material	Silver alloy (AgNi)	
[le] Rated Operational Current	16 A (AC-1/DC-1) NO conforming to IEC 8 A (AC-1/DC-1) NC conforming to IEC	
Minimum Switching Current	10 mA	
Maximum Switching Voltage	300 V DC conforming to IEC	
Minimum Switching Voltage	12 V	
Maximum Switching Capacity	4000 VA/448 W	
Resistive Rated Load	16 A at 250 V AC 16 A at 28 V DC	
Minimum Switching Capacity	120 mW at 10 mA, 12 V	
Operating Rate	<= 600 cycles/hour under load <= 18000 cycles/hour no-load	
Mechanical Durability	1000000 cycles	
Electrical Durability	100000 cycles, 16 A at 250 V, AC-1 NO 100000 cycles, 8 A at 250 V, AC-1 NC	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Operating Time	20 ms operating 20 ms reset	
	20 ms reset	
Average Coil Consumption	0.75 VA AC	
Drop-Out Voltage Threshold	>= 0.15 Uc AC	
Safety Reliability Data	B10d = 100000	
Protection Category	RTI	
Test Levels	Level A group mounting	
Operating Position	Any position	
Net Weight	0.014 kg	
Sale Per Indivisible Quantity	10	
Device Presentation	Complete product	

Environment

Dielectric Strength	1000 V AC between contacts 2500 V AC between poles 5000 V AC between coil and contact
Standards	IEC 61810-1 CSA C22.2 No 14 UL 508
Product Certifications	UL CSA EAC
Ambient Air Temperature For Storage	-4085 °C
Vibration Resistance	+/- 1 mm (f= 1055 Hz) conforming to IEC 60068-2-6
Ip Degree Of Protection	IP40 conforming to IEC 60529
Shock Resistance	10 gn (duration = 11 ms) for not operating conforming to IEC 60068-2-27 5 gn (duration = 11 ms) for in operation conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-4070 °C (AC)

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.7 cm
Package 1 Width	2.5 cm
Package 1 Length	31.1 cm
Package 1 Weight	15.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.7 cm
Package 2 Width	2.5 cm
Package 2 Length	31.1 cm
Package 2 Weight	159.0 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	350
Package 3 Height	15.0 cm

Package 3 Width	15.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.755 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations


Dimensions Drawings

Dimensions



Connections and Schema

Wiring Diagram




(1) Terminals 11 and 21,14 and 24,12 and 22 must be linked for this references

NOTE: For DC input, A1 have to be +, otherwise it would short circuit from protection module

Performance Curves

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load




X Switching capacity (kVA)

Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor $\cos\varphi)$



Y Reduction coefficient (A) Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

Note : These are typical curves, actual durability depends on load, environment, duty cycle, etc.