# **Product datasheet**

Specifications





trip unit MicroLogic 2.2 AB for ComPact NSX 160/250 circuit breakers, electronic, rating 160 A, 4 poles 4d

LV434551

() Discontinued

() Discontinued on: Nov 20, 2023

# Main

Range	ComPact
Range Of Product	ComPact NSX100250
Product Or Component Type	Trip unit
Trip Unit Name	MicroLogic 2.2 AB
Trip Unit Technology	Electronic
Range Compatibility	ComPact NSX160 ComPact NSX250
Device Application	Special application
Number Of Poles	4P
Protected Poles Description	3t + N/2 3t 4t
Neutral Position	Left
Trip Unit Protection Functions	LSol
Protection Type	L : for overload protection (long time) So : for short time short-circuit protection with fixed delay I : for instantaneous short-circuit protection
Trip Unit Rated Current	160 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz

# Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable
[Ir] Long-Time Protection Pick-Up Adjustment Range	90160 A
Long-Time Protection Delay Adjustment Type Tr	Fixed
[Tr] Long-Time Protection Delay Adjustment Range	15 s at 1.5 x lr 0.35 s at 7.2 x lr 0.5 s at 6 x lr
Thermal Memory	20 minutes before and after tripping
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Protection Pick- Up Adjustment Range	1.510 x lr

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Short-Time Protection Delay Adjustment Type Tsd	Fixed
[Tsd] Short-Time Protection Delay Adjustment Range	0.02 s
Instantaneous Protection Pick-Up Adjustment Type li	Fixed
[li] Instantaneous Protection Pick- Up Adjustment Range	1600 A
Earth-Leakage Protection	Without
Neutral Protection Settings	0.5 x lr (3t + N/2) 1 x lr (4t) No protection (3t)
Zone Selective Interlocking Zsi	Without
Local Signalling	Flashing LED (green) for ready to operate LED 105 % Ir (red) for overload LED 90 % Ir (orange) for overload

### Environment

Standards	UL 508 EN/IEC 60947-2
Product Certifications	Marine EAC CCC
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	10.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	570.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	23
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	13.6 kg

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information