

Product datasheet

Specifications



APC Easy UPS On-Line, 2000VA/
1600W, Tower, 230V, 4x IEC C13
outlets, Intelligent Card Slot, LCD

SRV2KI

Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	1600 W
Rated Power In Va	2000 VA
Input Connection Type	IEC 60320 C14
Output Connection Type	4 IEC 60320 C13
Cable Length	1.50 m
Number Of Cables	1
Provided Equipment	1 IEC 60320 C13 to Schuko power cable 1 IEC 60320 C13 to C14 power cable 1 USB cable 1 RS-232 configuration cable user manual

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Lead-acid battery
Battery Voltage	48 V
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	4 h
Battery Life	3...5 year(s)
Replacement Battery	APCRBCV204
Battery Charger Power	70 W rated

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Max Runtime	4 min
Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	23.8 cm
Width	14.5 cm
Depth	40 cm
Net Weight	16.8 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Usb Compatible	Yes
Mounting Position	Vertical

Input

Input Voltage Limits	110...285 V half load 160...280 V full load
Network Frequency	40...70 Hz auto sensing

Output

Maximum Configurable Power In Va	2000 VA
Maximum Configurable Power In W	1600 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Harmonic Distortion	3 %
Ups Type	Double conversion online
Wave Type	Sine wave
Efficiency	88 % (full load)
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass Type	Internal bypass (automatic and manual)
Crest Factor	3 : 1

Conformance

Product Certifications	CE UKCA EAC TISI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m
Acoustic Level	50 dBA
Heat Dissipation	745 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control Panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge Energy Rate	600 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	35.5 cm
Package 1 Width	23.5 cm
Package 1 Length	52.5 cm
Package 1 Weight	18.1 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Energy Efficient Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information