

Product datasheet

Specifications



cartridge M221 - 2 analog voltage outputs - I/O extension

TMC2AQ2V

Main

| | |
|---------------------------|---------------------------|
| Range Of Product | Modicon M221 |
| Product Or Component Type | Analogue output cartridge |
| Product Compatibility | Modicon M221C |

Complementary

| | |
|--|---|
| Analogue Output Number | 2 |
| Analogue Output Type | Voltage: 0...10 V |
| Analogue Output Resolution | 12 bits |
| LSb Value | 2.44 mV 0...10 V voltage |
| Load Type | Resistive |
| Load Impedance Ohmic | >= 2 kOhm |
| Conversion Time | 20 ms |
| Stabilisation Time | 40 ms |
| Absolute Accuracy Error | +/- 1 % of full scale +/- 0.3 % of full scale at 25 °C |
| Temperature Drift | +/- 0.02 %FS/°C |
| Repeat Accuracy | +/- 0.4 %FS |
| Non-Linearity | +/- 0.01 %FS |
| Cross Talk | <= 1 LSB |
| Type Of Cable | Twisted shielded pairs cable |
| Electrical Connection | 3 x 1.5 mm² 2 screw terminal blocks with pitch 3.81 mm adjustment for outputs |
| Maximum Cable Distance Between Devices | Twisted shielded pairs cable: <30 m for output |
| Insulation | Non-insulated between analogue output and internal logic |
| Height | 41 mm |
| Depth | 15 mm |
| Width | 35 mm |
| Net Weight | 0.015 kg |

Environment

| | |
|-------------------------|-------|
| Immunity To Microbreaks | 10 ms |
|-------------------------|-------|

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.5 cm |
| Package 1 Width | 7.0 cm |
| Package 1 Length | 4.6 cm |
| Package 1 Weight | 20.0 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 75 |
| Package 2 Height | 15 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 3.356 kg |
| Unit Type Of Package 3 | P06 |
| Number Of Units In Package 3 | 1200 |
| Package 3 Height | 75 cm |
| Package 3 Width | 60 cm |
| Package 3 Length | 80 cm |
| Package 3 Weight | 75 kg |

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | |
|------------------------------|-----|
| ✓ Toxic Heavy Metal Free | |
| ✓ Mercury Free | |
| ✓ Rohs Exemption Information | Yes |
| ✓ Pvc Free | |

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |