Product datasheet

Specification





EasyLogic - Digital Panel Meter DM3000 - Voltmeter - three phases

METSEDM3210

Main

Range	EasyLogic
Product Name	EasyLogic DM3000
Device Short Name	DM3210
Product Or Component Type	Voltmeter
Device Application	GenSet Test laboratories Load control

Complementary

Poles Description	3P 3P + N
Type Of Measurement	Voltage
Type of measurement	Vollage
[Us] Rated Supply Voltage	100230 V AC +/- 20 % 100230 V DC +/- 20 %
	100230 V DC 1 7- 20 %
Supply Frequency	50/60 Hz +/- 5 Hz
Network Frequency	50 Hz
	60 Hz
Maximum Power Consumption In Va	3 VA at 230 V AC
Display Type	LED
Display Digits	4
Full Scale Display	999.9
Control Type	Selector switch built-in
Analogue Input Type	Voltagethree phase
Measurement Voltage	25277 V AC phase to neutral, 50/60 Hz +/- 5 Hz 44480 V AC phase to phase, 50/60 Hz +/- 5 Hz
Accuracy	Voltage +/- 0.5 % of full scale for class 0.5
Device Mounting	Flush
Mounting Support	Panel
Type Of Installation	Indoor
Measurement Category	Category III
Standards	IEC 61326
Product Certifications	CE conforming to IEC 61010-1

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Electromagnetic Compatibility	Conducted and radiated emissions class A conforming to CISPR 11 Electrostatic discharge conforming to IEC 61000-4-2 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Harmonics conforming to IEC 61000-3-2 Limitation of voltage changes, voltage fluctuations and flicker in low-voltage conforming to IEC 61000-3-3
Ip Degree Of Protection	Front panel: IP50 Body: IP30
Relative Humidity	595 %
Pollution Degree	2
Ambient Air Temperature For Operation	-1060 °C
Ambient Air Temperature For Storage	-2570 °C
Colour	Black
Width	96 mm
Height	96 mm
Depth	38 mm
Cut-Out Dimensions	92 x 92 mm
Net Weight	170 g

Packing Units

r adming dime	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.6 cm
Package 1 Width	9.6 cm
Package 1 Length	4.35 cm
Package 1 Weight	256 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.1 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	128
Package 3 Height	105 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	32.8 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information