

Product datasheet

Specifications



50MM BLACK BASE UNIT

XVPC21

⚠ Discontinued on: Jan 23, 2021

⚠ Discontinued

Main

Range Of Product	Harmony XVP Universal
Product Or Component Type	Base unit with cover
Mounting Diameter	50 mm
Component Name	XVPC
Housing Colour	Black
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with or without cable end

Complementary

Fixing Mode	Direct or tube fixing
Material	Acrylic butadiene styrene + polycarbonate: base unit Polyamide: cover unit
Assembly Style	Customer assembly, up to 5 units
Marking	CE
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Terminals Description Iso N°1	(COM-3)PW (COM-4)PW (COM-5)PW (GND)GROUND (COM-1)PW (COM-2)PW
Net Weight	0.125 kg

Environment

Product Certifications	cULus
Standards	EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C

Contractual warranty

Warranty	18 months
----------	-----------


Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting and Clearance

Base Unit for Indicator Banks


Panel Cut-out for Direct Fixing



Connections and Schema

Indicator Bank

Wiring Diagram



- +/1 Power supply for first unit
- +/2 Power supply for second unit
- +/3 Power supply for third unit
- +/4 Power supply for fourth unit
- +/5 Power supply for fifth unit
- /C Common for all units