

Inductive proximity sensors XS, inductive sensor XS5 M18, L39mm, brass, Sn5mm, 12...24 VDC, cable 2 m

XS518B1PAL2

(!) Discontinued

Main

Mani		
Range of product	Telemecanique Inductive proximity sensors XS	
Series name	General purpose	
Sensor type	Inductive proximity sensor	
Device application	-	
Sensor name	XS5	
Sensor design	Cylindrical M18	
Size	39 mm	
Body type	Fixed	
Detector flush mounting acceptance	Flush mountable	
Material	Metal	
Type of output signal	Discrete	
Wiring technique	3-wire	
[Sn] nominal sensing distance	5 mm	
Discrete output function	1 NO	
Output circuit type	DC	
Discrete output type	PNP	
Electrical connection	Cable	
Cable length	2 m	
[Us] rated supply voltage	1224 V DC with reverse polarity protection	
Switching capacity in mA	<= 200 mA DC with overload and short-circuit protection	
IP degree of protection	IP68 double insulation conforming to IEC 60529 IP69K conforming to DIN 40050	

Complementary

Thread type	M18 x 1	
Detection face	Frontal	
Front material	PPS	
Enclosure material	Nickel plated brass	
Operating zone	04 mm	
Differential travel	115% of Sr	

Cable composition	3 x 0.34 mm²	
Wire insulation material	PVC	
Status LED	Output state: 1 LED (yellow)	
Supply voltage limits	1036 V DC	
Switching frequency	<= 2000 Hz	
Maximum voltage drop	<2 V (closed)	
Current consumption	<= 10 mA no-load	
Maximum delay first up	10 ms	
Maximum delay response	0.15 ms	
Maximum delay recovery	0.35 ms	
Marking	CE	
Threaded length	28 mm	
Length	39 mm	
Net weight	0.12 kg	

Environment

Product certifications	UL CSA	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn amplitude = +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn for 11 ms conforming to IEC 60068-2-27	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.600 cm
Package 1 Width	11.300 cm
Package 1 Length	11.700 cm
Package 1 Weight	94.000 g
Unit Type of Package 2	S03
Number of Units in Package 2	44
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.910 kg

Contractual warranty

Warranty (in months) 18



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Materials and Substances		
Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
SCIP Number	3bc2f5da-1620-4d53-878c-410a857f3212	
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Use Again

○ Repack and remanufacture		
Take-back	No	

Dimensions Drawings


Dimensions




Mounting and Clearance

Minimum Mounting Distances


Side by side



e (1) \geq 10 mm/0.39 in. Face to face




e (2) ≥ 60 mm/2.36 in. Facing a metal object



e (3) ≥ 15 mm/0.60 in

Mounting



(1) Bending cable: 4 x external cable diameter


Product data sheet

XS518B1PAL2

Connections and Schema

Wiring Schemes

PNP




BU : Blue BN : Brown BK : Black

Performance Curves

Performance Curves

Standard Steel Target: 18x18x1 mm



- (1) Pick-up points
- (2) Drop-out points (object approaching from the side)
- (y) Sensing distance in mm