


Product datasheet

Specifications



MOUNT.PLATE 2 NSX/CVS/INS FIXED/PLUGIN TOGGLE/ROT/ MOT -3P/4P 630A VERTICAL W650

03461

⚠ Discontinued

⚠ Discontinued on: 14 May 2023

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Installed Device

[illegible]

ComPact: drawout NSX630 with earth leakage protection - control: toggle - vertical installation

ComPact: drawout NSX630 with earth leakage protection - control: direct front rotary handle - vertical installation

ComPact: drawout NSX630 with earth leakage protection - control: motor mechanism - vertical installation

Poles Description	1 x 3P: fixed CVS400 vertical installation 1 x 4P: fixed CVS400 vertical installation 1 x 3P: fixed CVS630 vertical installation 1 x 4P: fixed CVS630 vertical installation 1 x 3P: fixed EZC400 vertical installation 1 x 4P: fixed EZC400 vertical installation 1 x 3P: fixed EZC630 vertical installation 1 x 4P: fixed EZC630 vertical installation 1 x 3P: fixed INS320...400 vertical installation 1 x 4P: fixed INS320...400 vertical installation 1 x 3P: fixed INS500...630 vertical installation 1 x 4P: fixed INS500...630 vertical installation 1 x 3P: fixed INV320...400 vertical installation 1 x 4P: fixed INV320...400 vertical installation 1 x 3P: fixed INV500...630 vertical installation 1 x 4P: fixed INV500...630 vertical installation 1 x 3P: fixed NSX400 vertical installation 1 x 4P: fixed NSX400 vertical installation 1 x 3P: fixed NSX630 vertical installation 1 x 4P: fixed NSX630 vertical installation 1 x 3P: plug-in NSX400 vertical installation 1 x 4P: plug-in NSX400 vertical installation 1 x 3P: drawout NSX400 vertical installation 1 x 4P: drawout NSX400 vertical installation 2 x 3P: fixed NSX400 vertical installation 2 x 4P: fixed NSX400 vertical installation 2 x 3P: plug-in NSX400 vertical installation 2 x 4P: plug-in NSX400 vertical installation 2 x 3P: drawout NSX400 vertical installation 2 x 4P: drawout NSX400 vertical installation 1 x 3P: plug-in NSX630 vertical installation 1 x 4P: plug-in NSX630 vertical installation 1 x 3P: drawout NSX630 vertical installation 1 x 4P: drawout NSX630 vertical installation 2 x 3P: fixed NSX630 vertical installation 2 x 4P: fixed NSX630 vertical installation 2 x 3P: plug-in NSX630 vertical installation 2 x 4P: plug-in NSX630 vertical installation 2 x 3P: drawout NSX630 vertical installation 2 x 4P: drawout NSX630 vertical installation 2 x 3P: fixed CVS630 vertical installation 2 x 4P: fixed CVS630 vertical installation 2 x 3P: fixed CVS400 vertical installation 2 x 4P: fixed CVS400 vertical installation
Number Of Vertical Modules [50 Mm]	13 module(s): CVS400 without earth leakage protection , direct in 650 mm Widecubicle 13 module(s): CVS630 without earth leakage protection , direct in 650 mm Widecubicle 13 module(s): EZC400, direct in 650 mm Widecubicle 13 module(s): EZC630, direct in 650 mm Widecubicle 10 module(s): INS320...400, direct in 650 mm Widecubicle 11 module(s): INS500...630, direct in 650 mm Widecubicle 10 module(s): INV320...400, direct in 650 mm Widecubicle 11 module(s): INV500...630, direct in 650 mm Widecubicle 11 module(s): NSX400 without earth leakage protection , direct in 650 mm Widecubicle 13 module(s): NSX630 without earth leakage protection , direct in 650 mm Widecubicle 15 module(s): CVS400 with earth leakage protection , direct in 650 mm Widecubicle 13 module(s): CVS400 with earth leakage protection , direct in 650 mm Widecubicle 15 module(s): CVS630 with earth leakage protection , direct in 650 mm Widecubicle 13 module(s): CVS630 with earth leakage protection , direct in 650 mm Widecubicle 13 module(s): NSX400 with earth leakage protection , direct in 650 mm Widecubicle 15 module(s): NSX630 with earth leakage protection , direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)

Width	650 mm
Height	372 mm
Net Weight	5.08 kg

[illegible]

25 Apr 2024

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	30.0 cm
Package 1 Length	58.0 cm
Package 1 Weight	5.017 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	29.0 cm
Package 2 Width	39.5 cm
Package 2 Length	59.5 cm
Package 2 Weight	15.795 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	36
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	194.16 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	RoHS Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information