Product datasheet

Specifications





analog input module Modicon Quantum - 8 I multirang

140AVI03000C

- (!) Discontinued on: 24 Sept 2022
- () To be end-of-service on: 31 Dec 2029

① Discontinued - Service only

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Analogue input module
Type Of Filter	Single pole low pass - 3 dB at 847 Hz +/- 20 %

Complementary

Complementary	
Analogue Input Number	8
Input Type	Differential
Addressing Requirement	9 input words
Analogue Input Type	Bipolar current: 20 mA
	Bipolar voltage: +/- 10 V
	Bipolar voltage: +/- 5 V
	Unipolar current: 020 mA
	Unipolar voltage: 010 V
	Unipolar voltage: 05 V
Analogue Input Resolution	16 bits +/- 10 V
	16 bits +/- 5 V
	16 bits 010 V
	16 bits 020 mA
	16 bits 05 V
	16 bits 20 mA
Linear Measuring Range	(input range) x 1.024 V
	(input range) x 1.024 mA
Absolute Maximum Input	50 V DC
	25 mA
Input Impedance	> 20 Ohm voltage
	250 MOhm +/- 0.03 %
Absolute Accuracy Error	+/- 0.03 %
	+/- 0.05 % of full scale maximum
Linearity Error	+/- 0.008 %
Accuracy Drift According To	+/- 0.0015 % of full scale/°C
Temperature	<= 0.004 % of full scale /°C
Common Mode Rejection	> - 80 dB 60 Hz
Isolation Between Channels And	500 Vrms AC for 60 s
Bus	750 V DC
Isolation Between Channels	135 Vrms AC
	200 V DC
Update Time	10 ms
Fault Type	Broken wire 420 mA
	Overtacking scale 15 V

Marking	CE
Local Signalling	1 LED (green) for bus communication is present (Active) 1 LED (red) for external fault 8 LEDs (green) for channel is turned on 8 LEDs (red) for channel fault
Bus Current Requirement	280 mA
Power Dissipation In W	2.2 W
Module Format	Standard
Net Weight	0.3 kg

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Standards	UL 508 CSA C22.2 No 142
Product Certifications	FM Class 1 Division 2 cUL
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 801000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.5 cm
Package 1 Length	31.0 cm
Package 1 Weight	474.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.318 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

Analog Input 8-Channel Bipolar Module

Wiring Diagram



N/C Not Connected