Product datasheet





Modicon Quantum low voltage discrete input module - 96 I positive logic

140DDI36400C

! Discontinued on: 24 Sept 2022

! To be end-of-service on: 31 Dec 2029

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Low voltage dc discrete input modules
Discrete Input Number	96

Complementary

Group Of Channels	6
Logic Input	Positive (sink)
Discrete Input Voltage	24 V DC
Input Voltage Limits	19.230 V
Voltage State 1 Guaranteed	1530 V DC
Voltage State 0 Guaranteed	5 V DC
Current State 1 Guaranteed	>= 2.5 mA
Current State 0 Guaranteed	>= 0.7 mA
Addressing Requirement	6 words
Input Impedance	6700 Ohm
Absolute Maximum Input	30 V continuous 50 V decaying pulse
Response Time	<= 2 ms from state 0 to state 1 <= 3 ms from state 1 to state 0
Power Dissipation	1.35 W + (0.13 x number of points on)
Isolation Between Group	500 Vrms for 1 minute
Local Signalling	1 LED (green) for bus communication is present (Active) 1 LED (red) for external fault detected (F) 96 LEDs (green) for input status
Marking	CE
Bus Current Requirement	270 mA
Module Format	Standard
Net Weight	0.3 kg

Environment

Protective Treatment Conformal coating Humiseal 1A33

Life Is On Schneider 23 Apr 2024

Standards	CSA C22.2 No 142 UL 508
Product Certifications	C-Tick FM Class 1 Division 2
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 802000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	00° °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.5 cm
Package 1 Length	32.0 cm
Package 1 Weight	529.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.058 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Mercury Free	
	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Product datasheet

140DDI36400C

Connections and Schema

24 Vdc 6x16 Input Module

6 Groups of 16 Inputs A...F (6 x HE 10 Connectors)

