



Main

Range	Prisma
Range of product	Prisma G
Product or component type	Mounting plate
Accessory / separate part category	Installation accessory
Range compatibility	Prisma G enclosure
Installation description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed device	EasyPact: fixed CVS400 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS630 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed EZC400 - control: toggle - vertical installation EasyPact: fixed EZC630 - control: toggle - vertical installation ComPact: fixed INS320...400 - control: direct front rotary handle - vertical installation ComPact: fixed INS500...630 - control: direct front rotary handle - vertical installation ComPact: fixed INV320...400 - control: direct front rotary handle - vertical installation ComPact: fixed INV500...630 - control: direct front rotary handle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 without earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS400 with earth leakage protection - control: toggle - vertical installation EasyPact: fixed CVS630 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 with earth leakage protection - control: toggle - vertical installation
Poles description	1 x 3P: fixed CVS400 vertical installation 1 x 4P: fixed CVS400 vertical installation 1 x 3P: fixed CVS630 vertical installation 1 x 4P: fixed CVS630 vertical installation 1 x 3P: fixed EZC400 vertical installation 1 x 4P: fixed EZC400 vertical installation 1 x 3P: fixed EZC630 vertical installation 1 x 4P: fixed EZC630 vertical installation 1 x 3P: fixed INS320...400 vertical installation 1 x 4P: fixed INS320...400 vertical installation 1 x 3P: fixed INS500...630 vertical installation 1 x 4P: fixed INS500...630 vertical installation 1 x 3P: fixed INV320...400 vertical installation 1 x 4P: fixed INV320...400 vertical installation

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

1 x 3P: fixed INV500...630 vertical installation
 1 x 4P: fixed INV500...630 vertical installation
 1 x 3P: fixed NSX400 vertical installation
 1 x 4P: fixed NSX400 vertical installation
 1 x 3P: fixed NSX630 vertical installation
 1 x 4P: fixed NSX630 vertical installation

Condition of using cable tie	Need additional plate (1M high) when installation of device is in vertical
Number of vertical modules [50 mm]	<p>12 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): CVS400 without earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s): CVS630 without earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): EZC400, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): EZC400, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s): EZC630, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s): EZC630, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s): INS320...400, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s): INS320...400, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): INS500...630, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): INS500...630, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s): INV320...400, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>10 module(s): INV320...400, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): INV500...630, direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): INV500...630, direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>12 module(s): NSX400 without earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s): NSX630 without earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>13 module(s): NSX630 without earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s): CVS400 with earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s): CVS400 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s): CVS630 with earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s): CVS630 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s): NSX400 with earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>14 module(s): NSX400 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s): NSX630 with earth leakage protection , direct with long terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)</p> <p>15 module(s): NSX630 with earth leakage protection , direct with long terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)</p>
Standards	IEC 61439-2
Product certifications	ASEFA

Complementary

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface finish	Smooth Matt
Colour	White (RAL 9001)

600 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle vertical 3P 1 direct with long terminal shield 13 0.311 mm
 600 mm Prisma G wall-mounted enclosure ComPact NSX630 without fixed toggle vertical 3P 1 direct with long terminal shield 13 0.311 mm
 600 mm Prisma G floor-standing enclosure ComPact NSX630 without fixed toggle vertical 4P 1 direct with long terminal shield 13 0.311 mm
 600 mm Prisma G wall-mounted enclosure ComPact NSX630 without fixed toggle vertical 4P 1 direct with long terminal shield 13 0.311 mm
 600 mm Prisma G floor-standing enclosure EasyPact CVS400 with fixed toggle vertical 3P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G wall-mounted enclosure EasyPact CVS400 with fixed toggle vertical 3P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G floor-standing enclosure EasyPact CVS400 with fixed toggle vertical 4P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G wall-mounted enclosure EasyPact CVS400 with fixed toggle vertical 4P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G floor-standing enclosure EasyPact CVS630 with fixed toggle vertical 3P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G wall-mounted enclosure EasyPact CVS630 with fixed toggle vertical 3P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G floor-standing enclosure EasyPact CVS630 with fixed toggle vertical 4P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G wall-mounted enclosure EasyPact CVS630 with fixed toggle vertical 4P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G floor-standing enclosure ComPact NSX400 with fixed toggle vertical 3P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G wall-mounted enclosure ComPact NSX400 with fixed toggle vertical 3P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G floor-standing enclosure ComPact NSX400 with fixed toggle vertical 4P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G wall-mounted enclosure ComPact NSX400 with fixed toggle vertical 4P 1 direct with long terminal shield 14 0.314 mm
 600 mm Prisma G floor-standing enclosure ComPact NSX630 with fixed toggle vertical 3P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G wall-mounted enclosure ComPact NSX630 with fixed toggle vertical 3P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G floor-standing enclosure ComPact NSX630 with fixed toggle vertical 4P 1 direct with long terminal shield 15 0.314 mm
 600 mm Prisma G wall-mounted enclosure ComPact NSX630 with fixed toggle vertical 4P 1 direct with long terminal shield 15 0.314 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.61 kg
Package 1 Height	9 cm
Package 1 width	26.5 cm
Package 1 Length	47 cm
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Weight	13.78 kg
Package 2 Height	30 cm
Package 2 width	40 cm
Package 2 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration

Environmental Disclosure

[Product Environmental Profile](#)

Halogen content performance

Halogen free product
