

Product datasheet

Specifications



power supply module Modicon Quantum - 125 V DC100..150 V standalone - 0.3..3 A

140CPS51100C

⚠ Discontinued on: 4 Jul 2022

⚠ To be end-of-service on: 31 Dec 2029

⚠ Discontinued

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Power supply module
Power Supply Type	Standalone

Complementary

Input Voltage	125 V (100...150 V) DC
Input Current	400 mA at 125 V
Inrush Current	10 A
Maximum Input Power Interruption	1 ms
Associated Fuse Rating	0.75 A, slow-blow
Output Voltage	5.1 V DC
Power Supply Output Current	0.3...3 A standalone
Output Overvoltage Protection	Internal
Output Overload Protection	Internal
Power Dissipation	2 + (3 x Iout) where Iout is in A
Local Signalling	1 LED (green) for power (PWR OK)
Marking	CE
Module Format	Standard
Net Weight	0.65 kg

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Standards	CSA C22.2 No 142 UL 508
Product Certifications	FM Class 1 Division 2 cUL
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 80...2000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	16.5 cm
Package 1 Length	31.0 cm
Package 1 Weight	692.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.384 kg


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

125 Vdc/3 A Power Supply Module

Wiring Diagram

