



auxiliary contact - 1 OC - 380..415 V - 6 A - for C60 ID

26924

! Discontinued on: 30 Jun 2021

(!) Discontinued

Main

| Range Of Product | Multi9 |
|-----------------------------|--|
| Product Or Component Type | OC contact |
| Device Short Name | OF |
| Signal Contacts Composition | 1 C/O |
| [In] Rated Current | AC-12 3 A at 380415 V, AC 50/60 Hz AC-12 6 A at 220240 V, AC 50/60 Hz |
| | DC-12 1 A at 130 V, DC |
| | DC-12 1.5 A at 60 V, DC |
| | DC-12 2 A at 48 V, DC |
| | DC-12 6 A at 24 V, DC |
| 9 Mm Pitches | 1 |

Complementary

| Mounting Mode | Fixed | |
|-------------------------|---|--|
| Mounting Support | DIN rail | |
| Height | 84 mm | |
| Width | 9 mm | |
| Depth | 73 mm | |
| Connections - Terminals | Clamp terminal2 cable(s) 1.5 mm² - flexible Clamp terminal2 cable(s) 1.5 mm² - rigid Clamp terminal1 cable(s) 0.52.5 mm² - flexible Clamp terminal1 cable(s) 0.52.5 mm² - rigid | |
| Wire Stripping Length | 9 mm | |
| Tightening Torque | 1 N.m | |

Environment

| Standards | EN/IEC 60947-5-1 |
|---------------------------------------|-------------------------------------|
| Product Certifications | ASTA KEMA |
| | ASEFA LCIE |
| Ip Degree Of Protection | IP20 conforming to EN/IEC 60947-5-1 |
| Pollution Degree | 3 conforming to EN/IEC 60947-5-1 |
| Tropicalisation | 2 conforming to EN/IEC 60947-5-1 |
| Relative Humidity | 95 % at 55 °C |
| Ambient Air Temperature For Operation | -2550 °C |

Ambient Air Temperature For -40...85 °C Storage

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2 cm |
| Package 1 Width | 8 cm |
| Package 1 Length | 8.8 cm |
| Package 1 Weight | 38 g |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| 9 | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |