



Price : 30,055.00 HKD



⚠ Discontinued

Commercial status

Discontinued on: 02 April 2021

End-of-service on: 03 April 2021

48035 has not been replaced. Please contact your customer care centre for more information.

Main

Range of product	Masterpact NW
Product or component type	Basic frame
Device short name	Masterpact NW12
Circuit breaker name	Masterpact NW12N1
Poles description	4P
Neutral position	Left
Network type	AC
Breaking capacity code	N1
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category B

Complementary

Network frequency	50/60 Hz
Control type	Push-button
Mounting mode	Fixed
[In] rated current	1250 A at 40 °C
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	12 kV conforming to IEC 60947-2
[Icm] rated short-circuit making capacity	187 kA 525 V AC at 50/60 Hz 187 kA 690 V AC at 50/60 Hz
[Ue] rated operational voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
Circuit breaker CT rating	1250 A
Breaking capacity	42 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 690 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 220...240 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 380...415 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	42 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2

	42 kA at 690 V AC 50/60 Hz conforming to IEC 60947-2
Protection type	Without protection
Mechanical durability	12500 cycles without maintenance conforming to IEC 60947-2 25000 cycles with maintenance conforming to IEC 60947-2
Electrical durability	10000 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2 10000 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
Connection pitch	115 mm
[Icw] rated short-time withstand current	22 kA 3 s conforming to IEC 60947-2 42 kA 1 s conforming to IEC 60947-2
Maximum breaking time	25 ms
Maximum closing response time	70 ms
Height	352 mm
Width	537 mm
Depth	297 mm

Environment

Standards	IEC 60947-2
Product certifications	ASTA ASEFA
Pollution degree	4 conforming to IEC 60664-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Package 1 Weight	47.252 kg
Package 1 Height	3.050 dm
Package 1 width	2.950 dm
Package 1 Length	4.950 dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------