# **Product datasheet**

Specification





circuit breaker Masterpact NW12H1 - 1250 A - 4 poles - fixed - w/o trip unit

48185

Price: 37,096.00 HKD

### Main

| Range                          | MasterPacT                       |
|--------------------------------|----------------------------------|
| Product Name                   | MasterPact NW                    |
| Circuit Breaker Name           | MasterPact NW12H1                |
| Product Or Component Type      | Circuit breaker                  |
| Device Application             | Power distribution protection    |
| Poles Description              | 4P                               |
| Neutral Position               | Right                            |
| Control Unit                   | Without control unit             |
| [In] Rated Current             | 1250 A at 40 °C                  |
| Performance Type               | H1 65 kA 440 V AC                |
| [Ue] Rated Operational Voltage | 690 V AC 50/60 Hz                |
| Suitability For Isolation      | Yes conforming to EN/IEC 60947-2 |
| Selectivity Category           | Category B                       |
| Control Type                   | Push-button                      |
| Mounting Mode                  | Fixed                            |

### Complementary

| [Icu] Rated Ultimate Short-Circuit       | 65 kA at 220/415 V AC 50/60 Hz  |
|------------------------------------------|---------------------------------|
| Breaking Capacity                        | 65 kA at 440 V AC 50/60 Hz      |
|                                          | 65 kA at 525 V AC 50/60 Hz      |
|                                          | 65 kA at 690 V AC 50/60 Hz      |
| [Ics] Rated Service Breaking             | 65 kA at 220/415 V AC 50/60 Hz  |
| Capacity                                 | 65 kA at 440 V AC 50/60 Hz      |
|                                          | 65 kA at 525 V AC 50/60 Hz      |
|                                          | 65 kA at 690 V AC 50/60 Hz      |
| [Icw] Rated Short-Time Withstand Current | 65 kA 1 s                       |
|                                          | 36 kA 3 s                       |
| [Icm] Rated Short-Circuit Making         | 143 kA 220/415 V AC at 50/60 Hz |
| Capacity                                 | 143 kA 440 V AC at 50/60 Hz     |
|                                          | 143 kA 525 V AC at 50/60 Hz     |
|                                          | 143 kA 690 V AC at 50/60 Hz     |
| Sensor Rating                            | 630 A                           |
| v                                        | 1250 A                          |
| [Ui] Rated Insulation Voltage            | 1000 V AC 50/60 Hz              |
| [Uimp] Rated Impulse Withstand Voltage   | 12 kV                           |
| Power Dissipation In W                   | 100 W                           |
|                                          |                                 |

| Maximum Breaking Time         | 25 ms                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Maximum Closing Response Time | 70 ms                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Mounting Support              | Backplate<br>Rails                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Upside Connection             | Front<br>Rear                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Downside Connection           | Front<br>Rear                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Connection Pitch              | 115 mm                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Mechanical Durability         | 12500 cycles without maintenance<br>25000 cycles with maintenance                                                                                                                                                                                                                                                                                                                                                                        |
| Electrical Durability         | 10000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 10000 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-2 AC-23A: 10000 cycles 440 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-23A: 10000 cycles 690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 AC-3: 6000 cycles 440/690 V AC 50/60 Hz without maintenance conforming to EN/IEC 60947-3 |
| Height                        | 352 mm                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Width                         | 537 mm                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Depth                         | 297 mm                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Net Weight                    | 65 kg                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Standards                     | EN/IEC 60947-1<br>EN/IEC 60947-2                                                                                                                                                                                                                                                                                                                                                                                                         |
| Product Certifications        | CE<br>CCC<br>EAC                                                                                                                                                                                                                                                                                                                                                                                                                         |

### **Environment**

| Ip Degree Of Protection               | IP30 conforming to IEC 60529                           |
|---------------------------------------|--------------------------------------------------------|
| Pollution Degree                      | 4 conforming to IEC 60664-1                            |
| Ambient Air Temperature For Operation | -2570 °C                                               |
| Ambient Air Temperature For Storage   | -4085 °C                                               |
| Operating Altitude                    | 02000 m without derating<br>2000 m5000 m with derating |

## **Packing Units**

| Unit Type Of Package 1       | PCE       |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 30.0 cm   |
| Package 1 Width              | 30.0 cm   |
| Package 1 Length             | 50.0 cm   |
| Package 1 Weight             | 54.252 kg |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration                                                                                                           |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive        | Compliant with Exemptions                                                                                                   |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information                         |
| Environmental Disclosure | Product Environmental Profile                                                                                               |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information                                                                                                     |