

Product datasheet

Specifications



I/O module MES114E - Sepam series 20, 40 - 10 inputs+ 4 outputs 110...125V

59651

Main

Module Type	Input/output module
Range Of Product	Sepam series 20 Sepam series 40 Sepam series 48
Device Short Name	MES114E

Complementary

Input/Output Type	10 inputs + 4 outputs 110...125 V
Logic Input Number	10 110 V 88...132 V AC 47...63 Hz 3 mA 58 V enhanced 10 110...125 V 88...150 V DC 3 mA 82 V enhanced
Number Of Outputs	1 control relay 3 indication relay

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output Type	<p>Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 0.005 kA $\cos \varphi > 0.3$ making capacity: < 15 A for 200 ms</p> <p>Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 0.008 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0002 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0005 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0007 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0001 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0002 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0003 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.004 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.006 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.008 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 250 V DC continuous current: 8 A breaking capacity: 0.0002 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.001 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.002 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.004 kA resistive making capacity: < 15 A for 200 ms</p> <p>Indication relay: 100...240 V AC 47.5...63 Hz continuous current: 2 A breaking capacity: 0.001 kA $\cos \varphi > 0.3$ making capacity: < 15 A for 200 ms</p> <p>Indication relay: 127 V DC continuous current: 2 A breaking capacity: 0.0005 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Indication relay: 127 V DC continuous current: 2 A breaking capacity: 0.0006 kA resistive making capacity: < 15 A for 200 ms</p> <p>Indication relay: 220 V DC continuous current: 2 A breaking capacity: 0.00015 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Indication relay: 220 V DC continuous current: 2 A breaking capacity: 0.0003 kA resistive making capacity: < 15 A for 200 ms</p> <p>Indication relay: 24 V DC continuous current: 2 A breaking capacity: 0.002 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Indication relay: 24 V DC continuous current: 2 A breaking capacity: 0.002 kA resistive making capacity: < 15 A for 200 ms</p> <p>Indication relay: 250 V DC continuous current: 2 A breaking capacity: 0.0002 kA resistive making capacity: < 15 A for 200 ms</p> <p>Indication relay: 48 V DC continuous current: 2 A breaking capacity: 0.001 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Indication relay: 48 V DC continuous current: 2 A breaking capacity: 0.001 kA resistive making capacity: < 15 A for 200 ms</p>
Net Weight	0.28 kg
Mechanical Robustness	<p>Earthquakes in operation (level: 2) : 1 Gn (vertical axes) conforming to IEC 60255-21-3</p> <p>Earthquakes in operation (level: 2) : 2 Gn (horizontal axes) conforming to IEC 60255-21-3</p> <p>Jolts de-energized (level: 2) : 20 Gn/16 ms conforming to IEC 60255-21-2</p> <p>Shocks de-energized (level: 2) : 30 Gn/11 ms conforming to IEC 60255-21-2</p> <p>Shocks in operation (level: 2) : 10 Gn/11 ms conforming to IEC 60255-21-2</p> <p>Vibrations de-energized (level: 2) : 2 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1</p> <p>Vibrations in operation (level: 2) : 1 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1</p> <p>Vibrations in operation (level: Fc) : 2 Hz...13.2 Hz, a = +/- 1 mm conforming to IEC 60068-2-6</p>
Auxiliary Connection Terminal	<p>Screw-type connectors1 cable(s) 0.2...2.5 mm²</p> <p>Screw-type connectors1 cable(s) 1.5 mm²</p> <p>Screw-type connectors1 cable(s) 2.5 mm²</p> <p>Screw-type connectors2 cable(s) 0.2...1 mm²</p> <p>Screw-type connectors2 cable(s) 1 mm²</p>

Environment

Electromagnetic Compatibility	<p>1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV MC and MD, conforming to ANSI C37.90.1</p> <p>1 MHz damped oscillating wave: (immunity tests-conducted disturbances), III, 2.5 kV MC, 1 kV MD, conforming to IEC 60255-22-1</p> <p>100 kHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV MC, 1 kV MD, conforming to IEC 61000-4-12</p> <p>Conducted disturbance emission: (emission tests), conforming to IEC 60255-25</p> <p>Conducted disturbance emission: (emission tests), B, conforming to EN 55022</p> <p>Disturbing field emission: (emission tests), conforming to IEC 60255-25</p> <p>Disturbing field emission: (emission tests), A, conforming to EN 55022</p> <p>Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 4 kV contact, conforming to ANSI C37.90.3</p> <p>Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 6 kV contact, conforming to IEC 60255-22-2</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), 4kV, 2.5 kHz, conforming to ANSI C37.90.1</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), A or B, 4kV, 2.5 kHz/ 2 kV, 5 kHz, conforming to IEC 60255-22-4</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), IV, 4kV, 2.5 kHz, conforming to IEC 61000-4-4</p> <p>Immunity to conducted RF disturbances: (immunity tests-conducted disturbances), 10 V, conforming to IEC 60255-22-6</p> <p>Immunity to magnetic fields at network frequency: (immunity tests-radiated disturbances), IV, 30 A/m (continuous)-300 A/m (13 s), conforming to IEC 61000-4-8</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), 10 V/m, 80 MHz... 1 GHz, conforming to IEC 60255-22-3</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), 35 V/m, 25 MHz... 1 GHz, conforming to ANSI C37.90.2 (1995)</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), III, 10 V/m, 80 MHz...2 GHz, conforming to IEC 61000-4-3</p> <p>Surges: (immunity tests-conducted disturbances), III, 2 kV MC, 1 kV MD, conforming to IEC 61000-4-5</p> <p>Voltage interruptions: (immunity tests-conducted disturbances), 100 %, 10 ms, conforming to IEC 60255-11</p>
-------------------------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Climatic Withstand	<p>Influence of corrosion/gaz test 4 (in operation) : 21 days, 75 % RH, 25 °C, 0.01 ppm H2S, 0.2 ppm SO2, 0.02 ppm NO2, 0.01 ppm Cl2 conforming to IEC 60068-2-60</p> <p>Continuous exposure to damp heat (in operation) : Ca: 10 days, 93 % RH, 40 °C (104 °F) conforming to IEC 60068-2-3</p> <p>Continuous exposure to damp heat (in storage) : Ca: 56 days, 93 % RH, 40 °C (104 °F) conforming to IEC 60068-2-3</p> <p>Exposure to cold (in operation) : Ab: - 25 °C (- 13 °F) conforming to IEC 60068-2-1</p> <p>Exposure to cold (in storage) : Ab: - 25 °C (- 13 °F) conforming to IEC 60068-2-1</p> <p>Exposure to dry heat (in operation) : Bb: 70 °C (158 °F) conforming to IEC 60068-2-2</p> <p>Exposure to dry heat (in storage) : Bb: 70 °C (158 °F) conforming to IEC 60068-2-2</p> <p>Influence of corrosion/gaz test 2 (in operation) : C: 21 days, 75 % RH, 25 °C (- 13 °F), 0.5 ppm H2S, 1 ppm SO2 conforming to IEC 60068-2-60</p> <p>Salt mist (in operation) : Kb/2 conforming to IEC 60068-2-52</p> <p>Temperature variation with specified variation rate (in operation) : Nb: - 25 °C to 70 °C (- 13 °F to 158 °F) 5 °C/min (41 °F/min) conforming to IEC 60068-2-14</p>
--------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	10.0 cm
Package 1 Length	25.0 cm
Package 1 Weight	412.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	9
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.14 kg

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information