# **Product datasheet**

Specifications





# Multi9, C60 UL489, MCB, 1 pole, 15 A, C Curve, 120 V, 10 kA, tunnel term

60112

() Discontinued on: 30 Jun 2021

Main

Wall	
Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60 UL489
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	15 A at 25 °C
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	5 kA AIR at 240 V AC conforming to UL 489 10 kA Icu at 240 V AC conforming to EN/IEC 60947-2 10 kA Icu at 240 V AC conforming to GB 14048.2 10 kA Icu at 60 V DC conforming to EN/IEC 60947-2 10 kA Icu at 60 V DC conforming to GB 14048.2 10 kA AIR at 120 V AC conforming to UL 489 10 kA AIR at 120 V AC conforming to CSA C22.2 No 5.2 5 kA AIR at 240 V AC conforming to CSA C22.2 No 5.2 10 kA AIR at 60 V DC conforming to CSA C22.2 No 5.2
Suitability For Isolation	Yes conforming to EN/IEC 60947-2

### Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	240 V AC
	60 V DC
	120 V AC
Magnetic Tripping Limit	8.5 x In +/- 20 % AC
	12 x ln +/- 20 % DC
Limitation Class	3 conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle

Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	107 mm
Width	18 mm
Depth	73 mm
Net Weight	0.11 kg
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal (top or bottom)2.525 mm <sup>2</sup> (AWG 14AWG 4) - rigid
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2.5 N.m top or bottom

### Environment

Standards	GB 14048.2 EN/IEC 60947-2 UL 489 CSA C22.2 No 5
Product Certifications	CSA CCC IEC UL
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Overvoltage Category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-3070 °C
Ambient Air Temperature For Storage	-4080 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	7.3 cm
Package 1 Length	14.2 cm
Package 1 Weight	134 g

### **Contractual warranty**

Warranty

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins