

Product datasheet

Specifications



Acti9/Multi9 - SP MCB/RCBO - 100A main bar - 8 way- Distribution Board

BF10-008

Main

Range	Acti9 HK enclosures
Product Or Component Type	Empty enclosure
Device Application	Low voltage electrical distribution
Door Type	Plain
Provided Equipment	enclosure DIN rail neutral bar earthing bar

Complementary

Protection Device Type	Residual current circuit breaker (RCCB) 1P Residual current circuit breaker with overcurrent protection (RCBO) 1P
[In] Rated Current	100 A (maximum)
[Ue] Rated Operational Voltage	240 V
Network Frequency	50/60 Hz
Total Number Of 18 Mm Modules	8
Connections - Terminals	Screw connection (neutral and earth in) 1...16 mm ² solid or flexible Screw connection (neutral and earth out) 1...10 mm ² solid or flexible
Type Of Rail	DIN
Enclosure Mounting	Surface
Number Of Ways	8 ways (outgoer) - 1P
Height	230 mm
Width	303 mm
Depth	91 mm
Ip Degree Of Protection	IP41

Environment

Standards	IEC 61439-3
-----------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation

