# **Product datasheet**





## Circuit breaker, ComPact NSX100F AC/DC, 18kA/240VAC, TMD trip unit 16A, 1 pole 1d

LV438562

! Discontinued on: 30 Jun 2023

! Discontinued

#### Main

Mani	
Range	ComPact
Product Name	ComPact NSX
Range Of Product	ComPact NSX100250 DC ComPact NSX100250
Device Short Name	NSX100F
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	1P
Protected Poles Description	1t
[In] Rated Current	16 A at 40 °C
[Ue] Rated Operational Voltage	250 V DC 277 V AC 50/60 Hz
Network Type	DC
Network Type	AC
Network Frequency	
	AC
Network Frequency	AC 50/60 Hz
Network Frequency Suitability For Isolation	So/60 Hz Yes conforming to EN/IEC 60947-2
Network Frequency Suitability For Isolation Utilisation Category [Icu] Rated Ultimate Short-Circuit	AC  50/60 Hz  Yes conforming to EN/IEC 60947-2  Category A  36 kA Icu at 250 V DC 1P conforming to IEC 60947-2 36 kA Icu at 125 V DC 1P conforming to IEC 60947-2
Network Frequency Suitability For Isolation Utilisation Category [Icu] Rated Ultimate Short-Circuit Breaking Capacity	AC  50/60 Hz  Yes conforming to EN/IEC 60947-2  Category A  36 kA Icu at 250 V DC 1P conforming to IEC 60947-2 36 kA Icu at 125 V DC 1P conforming to IEC 60947-2 18 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Network Frequency Suitability For Isolation Utilisation Category [Icu] Rated Ultimate Short-Circuit Breaking Capacity Performance Level	AC  50/60 Hz  Yes conforming to EN/IEC 60947-2  Category A  36 kA Icu at 250 V DC 1P conforming to IEC 60947-2 36 kA Icu at 125 V DC 1P conforming to IEC 60947-2 18 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 F 18 kA 240 V AC
Network Frequency Suitability For Isolation Utilisation Category [Icu] Rated Ultimate Short-Circuit Breaking Capacity  Performance Level Trip Unit Name	AC  50/60 Hz  Yes conforming to EN/IEC 60947-2  Category A  36 kA Icu at 250 V DC 1P conforming to IEC 60947-2 36 kA Icu at 125 V DC 1P conforming to IEC 60947-2 18 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2  F 18 kA 240 V AC  TM-D

### Complementary

[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	36 kA at 250 V DC conforming to IEC 60947-2 36 kA at 125 V DC conforming to IEC 60947-2 18 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	20000 cycles

Life Is On Schneider 25 Apr 2024

Electrical Durability	10000 cycles at 277 V In 20000 cycles at 277 V In/2
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	35 mm
Protection Type	for overload protection (thermal) for short-circuit protection (magnetic)
Trip Unit Rating	16 A at 40 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Fixed
[Ir] Long-Time Protection Pick-Up Adjustment Range	1 ln
[Im] Magnetic Protection Pick-Up Range	190 A
Earth-Leakage Protection	Without
Width (W)	35 mm
Height (H)	161 mm
Depth (D)	86 mm

### **Environment**

Standards	EN/IEC 60947
Product Certifications	CCC EAC Marine
Overvoltage Category	Class II
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-50…85 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	13.0 cm
Package 1 Length	17.5 cm
Package 1 Weight	742.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm

Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9 391 kg

### **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information