Product datasheet

Specifications





Miniature circuit breaker (MCB), Multi9 C60SP, 2P, 50A, C curve, 5kA (UL1077), 10kA (IEC/EN 60947-2)

M9F22250

Main

Mani	
Range	Multi9
Product Name	Multi9 C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60SP
Device Application	Distribution
Poles Description 2P	
Number Of Protected Poles	2
[In] Rated Current	50 A at 25 °C conforming to EN/IEC 60947-2
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	С
Breaking Capacity	10 kA AIR at 240 V AC conforming to UL 1077 10 kA AIR at 240 V AC conforming to CSA C22.2 No 235 6 kA Icu at 440 V AC conforming to EN/IEC 60947-2 10 kA Icu at 415 V AC conforming to EN/IEC 60947-2 20 kA Icu at 240 V AC conforming to EN/IEC 60947-2 6 kA Icu at 440 V AC conforming to GB 14048.2 10 kA Icu at 415 V AC conforming to GB 14048.2 20 kA Icu at 240 V AC conforming to GB 14048.2 5 kA AIR at 480Y/277 V AC conforming to UL 1077 5 kA AIR at 480Y/277 V AC conforming to CSA C22.2 No 235
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Standards	EN/IEC 60947-2 GB 14048.2 UL 1077 CSA C22.2 No 235
Product Certifications	IEC CCC UR CSA

Complementary

[Ue] Rated Operational Voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 440 V AC 50/60 Hz	
Magnetic Tripping Limit	8.5 x In +/- 20 % AC	
[Ics] Rated Service Breaking Capacity	4.5 kA 75 % conforming to EN/IEC 60947-2 - 440 V AC 7.5 kA 75 % conforming to EN/IEC 60947-2 - 415 V AC 15 kA 75 % conforming to EN/IEC 60947-2 - 240 V AC 4.5 kA 75 % conforming to GB 14048.2 - 440 V AC 7.5 kA 75 % conforming to GB 14048.2 - 415 V AC	

24 Apr 2024 Life Is On Schneider

15 kA 75 % conforming to GB 14048.2 - 240 V AC

[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	72 mm
Colour	Grey
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal (top or bottom)135 mm² (AWG 18AWG 2) - rigid Tunnel type terminal (top or bottom)125 mm² (AWG 18AWG 3) - flexible with ferrule Tunnel type terminal (top or bottom)125 mm² (AWG 18AWG 3) - flexible
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	3.5 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	02000 m
Ambient Air Temperature For Operation	-3070 °C
Ambient Air Temperature For Storage	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	3.6 cm
Package 1 Length	8.5 cm
Package 1 Weight	245.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	8.0 cm

Package 2 Width	8.8 cm
Package 2 Length	22.5 cm
Package 2 Weight	1.516 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	18.696 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
Ø	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations