



Main

Range	TeSys
Product name	TeSys VARIO
Device short name	V
Product or component type	Switch body
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	AC DC
Network frequency	50/60 Hz
Suitability for isolation	Yes

Complementary

Mounting support	Symmetrical rail Plate
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	125 A
[Ithe] conventional enclosed thermal current	100 A
[Ie] rated operational current	68.5 A AC-23 Ue: 400 V
Rated operational power in W	22 kW at 230...240 V (AC-3) 30 kW at 400...415 V (AC-3) 30 kW at 690 V (AC-3) 37 kW at 500 V (AC-3) 37 kW at 690 V (AC-23A) 45 kW at 500 V (AC-23A) 22 kW at 230...240 V (AC-23A) 37 kW at 400...415 V (AC-23A)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Intermittent duty class	30
Making capacity (I Rms)	1250 A at 400 V AC-21A 1250 A at 400 V AC-22A 1250 A at 400 V AC-23A
[Icm] rated short-circuit making capacity	2.8 kA at 400 V at Ipeak
[Icw] rated short-time withstand Rms current	1500 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 125 A aM 10 kA at 400 V - associated fuse 125 A gG
Breaking capacity	1000 A at 400 V (AC-21A) 1000 A at 400 V (AC-22A) 1000 A at 400 V (AC-23A)
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-21 30000 cycles DC-1...5
Connections - terminals	Power circuit: screw clamp terminals70 mm ² - flexible - with cable end Power circuit: screw clamp terminals95 mm ² - solid
Tightening torque	Power circuit: 22.6 N.m - on screw clamp terminals
Height	125 mm
Width	90 mm
Depth	90 mm
Net weight	0.9 kg

Environment

Standards	IEC 60947-3
Product certifications	CSA UL GL
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.056 kg
Package 1 Height	10 cm
Package 1 width	11.5 cm
Package 1 Length	13.3 cm
Unit Type of Package 2	S02
Number of Units in Package 2	6
Package 2 Weight	6.636 kg
Package 2 Height	15 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P06
Number of Units in Package 3	96
Package 3 Weight	114.315 kg
Package 3 Height	80 cm
Package 3 width	80 cm
Package 3 Length	60 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------