



Glavno

Range	TeSys
Product name	TeSys F
Product or component type	Contactors
Device short name	LC1F
Contactors application	Resistive load Motor control
Utilisation category	AC-1 AC-4 AC-3
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	≤ 460 V DC ≤ 690 V AC 50/60 Hz
[Ie] rated operational current	315 A (≤ 40 °C) at ≤ 440 V AC-1 225 A (≤ 55 °C) at ≤ 440 V AC-3
Motor power kW	110 kW at 380...400 V AC 50/60 Hz AC-3 110 kW at 415 V AC 50/60 Hz AC-3 110 kW at 440 V AC 50/60 Hz AC-3 129 kW at 500 V AC 50/60 Hz AC-3 63 kW at 220...230 V AC 50/60 Hz AC-3 40 kW at 400 V AC 50/60 Hz AC-4 129 kW at 660...690 V AC 50/60 Hz AC-3
[Uc] control circuit voltage	24 V DC
Coil type	Standard

Complementary

[Uimp] rated impulse withstand voltage	8 kV
Overvoltage category	III
[Ith] conventional free air thermal current	315 A at ≤ 40 °C
Rated breaking capacity	1800 A conforming to IEC 60947-4-1

[I _{cw}] rated short-time withstand current	1800 A ≤ 40 °C 10 s 1000 A ≤ 40 °C 30 s 850 A ≤ 40 °C 1 min 560 A ≤ 40 °C 3 min 440 A ≤ 40 °C 10 min
Associated fuse rating	315 A gG at ≤ 440 V 250 A aM at ≤ 440 V
Average impedance	0.32 mOhm at 50 Hz - I _{th} 315 A
[U _i] rated insulation voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power dissipation per pole	16 W AC-3 32 W AC-1
Mounting support	Plate
Standards	EN 60947-4-1 JIS C8201-4-1 EN 60947-1 IEC 60947-4-1 IEC 60947-1
Product certifications	LROS (Lloyds register of shipping) RINA RMRoS DNV BV UL CSA ABS CB
Connections - terminals	Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Power circuit: connector 1 cable(s) 185 mm ² Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit: screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Power circuit: lugs-ring terminals 1 cable(s) 185 mm ² Power circuit: bolted connection Power circuit: bar 2 x (32 x 4 mm)
Tightening torque	Power circuit: 35 N.m Control circuit: 1.2 N.m
Control circuit voltage limits	0.15...0.2 U _c at 55 °C drop-out 0.85...1.1 U _c at 55 °C operational
Inrush power in W	800 W at 20 °C
Hold-in power consumption in W	5 W at 20 °C
Heat dissipation	5 W
Operating time	30...40 ms closing 30...50 ms opening
Mechanical durability	10 Mcycles
Operating rate	2400 cyc/h at ≤ 55 °C

Environment

IP degree of protection	IP20 front face with shrouds (ordered separately) conforming to IEC 60529 IP20 front face with shrouds (ordered separately) conforming to VDE 0106
Protective treatment	TH
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C
Operating altitude	3000 m without derating
Mechanical robustness	Vibrations resistance contactor open 2 Gn, 5...300 Hz Shocks resistance contactor closed 15 Gn for 11 ms Vibrations resistance contactor closed 5 Gn, 5...300 Hz Shocks resistance contactor open 7 Gn for 11 ms

Height	197 mm
Width	168.5 mm
Depth	181 mm
Product weight	4.75 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0843 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Ekološki profil proizvoda
Product end of life instructions	Available Informacije o kraju vijeka trajanja

Contractual warranty

Warranty period	18 months
-----------------	-----------