


Product datasheet

Specifications



FRONT PLATE INS-INV250 VERTICAL W300 9M

03251

Discontinued on: Jun 15, 2023

Discontinued

Main

| | |
|------------------------------------|--|
| Range | Prisma |
| Range Of Product | Prisma G |
| Product Or Component Type | Front plate |
| Accessory / Separate Part Category | Installation accessory |
| Range Compatibility | Prisma Prisma G duct |
| Type Of Front Plate | Cut-out |
| Installed Device | ComPact: fixed INV100 - control: direct front rotary handle - vertical installation ComPact: fixed INV160 - control: direct front rotary handle - vertical installation ComPact: fixed INV200 - control: direct front rotary handle - vertical installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation ComPact: fixed INS250 - control: direct front rotary handle - vertical installation |
| Poles Description | 1 x 4P: mounting plate support: INV100 vertical installation 1 x 4P: mounting plate support: INV160 vertical installation 1 x 4P: mounting plate support: INV200 vertical installation 1 x 4P: mounting plate support: INV250 vertical installation 1 x 3P: mounting plate support: INS250 vertical installation 1 x 4P: mounting plate support: INS250 vertical installation 1 x 3P: mounting plate support: INV100 vertical installation 1 x 3P: mounting plate support: INV160 vertical installation 1 x 3P: mounting plate support: INV200 vertical installation 1 x 3P: mounting plate support: INV250 vertical installation |
| Operating Position | Vertical |

Complementary

| | |
|------------------------------------|--|
| Enclosure/Cubicle Description | Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm |
| Connection Position | Direct connection |
| Number Of Vertical Modules [50 Mm] | 9 |
| Standards | IEC 61439-2 IEC 61439-1 |
| Product Certifications | ASEFA |
| Material | Steel |
| Surface Finish | Matt Smooth |
| Protective Treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Colour | White (RAL 9001) |
| Height | 450 mm |
| Width | 300 mm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|--|
| Net Weight | 0.94 kg |
| Quantity Per Set | Set of 1 |
| Functional Unit | 300 mm Prisma G floor-standing duct ComPact INS250 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INS250 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INS250 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INS250 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV100 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV100 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV100 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV160 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV160 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV200 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV200 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV250 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV250 fixed direct front rotary handle vertical 3P 1 direct with long terminal shield 9 300 mm Prisma G floor-standing duct ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 300 mm Prisma G wall-mounted duct ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct with long terminal shield 9 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.000 cm |
| Package 1 Width | 26.000 cm |
| Package 1 Length | 47.000 cm |
| Package 1 Weight | 940.000 g |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 17.000 cm |
| Package 2 Width | 27.000 cm |
| Package 2 Length | 53.000 cm |
| Package 2 Weight | 9.740 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 120 |
| Package 3 Height | 48.000 cm |
| Package 3 Width | 80.000 cm |

| | |
|------------------|------------|
| Package 3 Length | 120.000 cm |
| Package 3 Weight | 116.880 kg |

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|------------------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| ✓ | Halogen Free Plastic Parts Product | |

Certifications & Standards

| | |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |