



Main

Range	Prisma
Range compatibility	Prisma P Prisma G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	<p>Compact : fixed NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : plug-in NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX400 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : drawout NSX630 without earth leakage protection - control: toggle - vertical installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : plug-in NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX400 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : drawout NSX630 without earth leakage protection - control: direct front rotary handle - vertical installation</p> <p>Compact : fixed NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : fixed NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : plug-in NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : plug-in NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : drawout NSX400 without earth leakage protection - control: motor mechanism - vertical installation</p> <p>Compact : drawout NSX630 without earth leakage protection - control: motor mechanism - vertical installation</p>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Easypact : fixed CVS400 without earth leakage protection - control: direct front rotary handle - vertical installation
 Easypact : fixed CVS630 without earth leakage protection - control: direct front rotary handle - vertical installation

Poles description	1 x 4P : mounting plate support : NSX400 vertical installation 1 x 3P : mounting plate support : CVS400 vertical installation 1 x 4P : mounting plate support : CVS400 vertical installation 1 x 3P : mounting plate support : CVS630 vertical installation 1 x 4P : mounting plate support : CVS630 vertical installation 1 x 3P : mounting plate support : NSX400 vertical installation 1 x 3P : mounting plate support : NSX630 vertical installation 1 x 4P : mounting plate support : NSX630 vertical installation
Operating position	Vertical

Complementary

Enclosure/Cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm, depth 400 mm
Connection position	Direct connection Linergy FC
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	450 mm
Width	500 mm
Product weight	1.72 kg
Material	Steel
Surface finish	Matt Smooth
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------