
Product datasheet

Specifications





Flat elbow, Canalis KTA, aluminium, 2500A, 3L+N+PER (Cu), high Icw, N2, 2 made to measure branches, right angle

KTA2500LP7E2

Main

Range	Canalis
Product Name	КТ
Product Or Component Type	Elbow
Busbar Description	Standard
Device Short Name	КТА
Device Application	Change direction
Material	Aluminium
[le] Rated Operational Current	2500 A at 35 °C
Polarity	3L + N + PER
Direction Change Type	direction 1: flat to right
Operating Angle	90 °
Earth Conductor	Reinforced
Short-Circuit Level	Reinforced version
Provided Equipment	Trunking unit Jointing unit

Complementary

Housing Material	Polyester film
Contacts Material	Copper
[Ue] Rated Operational Voltage	1000 V
Network Frequency	50/60 Hz
[Ui] Rated Insulation Voltage	1000 V
[Icw] Rated Short-Time Withstand Current	113 kA
[lpk] Rated Peak Withstand Current	248 kA
Radiated Magnetic Field	1.6 µT
Thermal Stress Limit	12769000 kA².s
Thdi	015 % 2500 A 1533 % 3200 A 33100 % 4000 A
Maximum Voltage Drop	<0.0024 V with power factor = 1 at 50 Hz with 1A for 100 m long <0.0025 V with power factor = 0.9 at 50 Hz with 1A for 100 m long <0.0024 V with power factor = 0.8 at 50 Hz with 1A for 100 m long <0.0022 V with power factor = 0.7 at 50 Hz with 1A for 100 m long
Neutral Position	Left

Standards	IEC 61439-6 IEC 61439-1
Dimension Type	Made to measure
Width	140 mm
Height	244 mm
Length	direction 1: 301600 mm direction 2: 3011100 mm
Colour	White (RAL 9001)
Linear Load	36 kg/m

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262
Derating Factor	035 °C (100 % of In) 3540 °C (97 % of In) 4045 °C (93 % of In) 4550 °C (90 % of In) 5055 °C (86 % of In)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.4 cm
Package 1 Width	65.0 cm
Package 1 Length	115.0 cm
Package 1 Weight	64.26 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information