



TeSys SK mini contactor - 2P (2 NO) - AC-3 - 690 V 6 A - 380 V AC coil

LC1SK0600Q7

! Discontinued on: Sep 30, 2020

① Discontinued

Main

Range	TeSys
Product Name	TeSys SK
Product Or Component Type	Mini contactor
Device Short Name	LC1SK
Contactor Application	Motor control Resistive load
Utilisation Category	AC-1 AC-3
Power Pole Contact Composition	2P
Pole Contact Composition	2 NO
[le] Rated Operational Current	6 A at <= 440 V AC AC-3 12 A (at <55 °C) AC AC-1
[Ue] Rated Operational Voltage	Power circuit: 690 V AC 50/60 Hz

Complementary

Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	380 V AC 50/60 Hz
[Ith] Conventional Free Air Thermal Current	12 A (at 55 °C) for power circuit
Irms Rated Making Capacity	66 A at 690 V AC conforming to IEC 60947 66 A at 690 V AC conforming to NF C 63-110
Rated Breaking Capacity	52 A at <= 400 V for power circuit conforming to NF C 63-110 52 A at <= 400 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	50 A 55 °C for power circuit
Associated Fuse Rating	16 A gl at <= 440 V for power circuit conforming to IEC 60947
Average Impedance	4 mOhm - Ith 12 A 50 Hz
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947 690 V conforming to VDE 0110 group C 690 V conforming to BS 5424 690 V conforming to UL 508 690 V conforming to CSA C22.2 No 14
Mounting Support	Rail
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1

Product Certifications	CB Scheme
	CE
	UKCA
	EAC
	cULus
Connections - Terminals	Power circuit: connector 1 cable(s) 0.356 mm²flexible with cable end
	Power circuit: connector 1 cable(s) 0.56 mm²flexible without cable end
	Power circuit: connector 1 cable(s) 1.56 mm²solid
	Power circuit: connector 2 cable(s) 0.351.5 mm²flexible with cable end
	Power circuit: connector 2 cable(s) 0.352.5 mm²flexible without cable end
	Power circuit: connector 2 cable(s) 1.54 mm²solid
Tightening Torque	0.8 N.m - on connector - with screwdriver pozidriv No 1
Operating Time	68 ms coil de-energisation and NO opening
	714 ms coil energisation and NO closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	1200 cyc/h
Control Circuit Voltage Limits	Operational: 0.851.1 Uc (at <50 °C)
	Drop-out: 0.20.75 Uc (at <50 °C)
Inrush Power In Va	16 VA (at 20 °C)
Hold-In Power Consumption In Va	4.2 VA (at 20 °C)
Heat Dissipation	1.4 W at 50/60 Hz

Environment

Ip Degree Of Protection	IP2X conforming to VDE 0106
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50015
Ambient Air Temperature For Operation	-2050 °C
Ambient Air Temperature For Storage	-5070 °C
Operating Altitude	2000 m without derating
Height	56 mm
Width	27 mm
Depth	55.5 mm
Net Weight	0.132 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	5.9 cm
Package 1 Length	3.3 cm
Package 1 Weight	120 g

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins