# **Product datasheet**





## EasyPact TVS differential thermal overload relay 48...65 A - class 10A

LRE359

### Main

Range	Easy TeSys	
Range Of Product	Easy TeSys Protect	
Product Or Component Type	Differential thermal overload relay	
Device Short Name	LRE	
Relay Application	Motor protection	
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0 conforming to IEC 60947-4-1	

## Complementary

Product Compatibility	LC1E6595
Network Type	AC
Network Frequency	5060 Hz
Mounting Support	Under contactor Plate, with specific accessories Rail, with specific accessories
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1
Signalling Function	Relay trip indicator
Thermal Protection Adjustment Range	4865 A
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1
Mechanical Robustness	Shocks: 6 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 GN conforming to IEC 60068-2-6
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
[Ue] Rated Operational Voltage	<= 690 V AC
Associated Fuse Rating	100 A gG for power circuit 63 A aM for power circuit 5 A gG for signalling circuit
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV
Local Signalling	Trip indicator
Control Type	Push-button red stop: Push-button green reset:
Temperature Compensation	-2060 °C

Life Is On Schneider May 15, 2024

Connections - Terminals	Signalling circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible without cable end Signalling circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end Signalling circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 1 435 mm² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 435 mm² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 1 435 mm² - cable stiffness: solid without cable end
Recommended Tightening Torque	Power circuit: 9 N.m - on screw clamp terminals Signalling circuit: 1.7 N.m - on screw clamp terminals
Height	54 mm
Width	70 mm
Depth	113 mm
Net Weight	0.46 kg

### **Environment**

Standards	IEC 60947-4-1 IEC 60947-5-1
Product Certifications	EAC
Protective Treatment	TH conforming to IEC 60068
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-2060 °C without derating conforming to IEC 60947-4-1 -2070 °C with derating
Ambient Air Temperature For Storage	-6080 °C
Fire Resistance	850 °C conforming to IEC 60068-2-1
Dielectric Strength	6 kV at 50 Hz conforming to IEC 60255-5
Electromagnetic Compatibility	Surge withstand: 6 kV conforming to IEC 60801-5

## **Packing Units**

Package 1 Height 8 cm  Package 1 Width 8.8 cm  Package 1 Length 12.7 cm  Package 1 Weight 479 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	•	
Package 1 Height 8 cm  Package 1 Width 8.8 cm  Package 1 Length 12.7 cm  Package 1 Weight 479 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Unit Type Of Package 1	PCE
Package 1 Width 8.8 cm  Package 1 Length 12.7 cm  Package 1 Weight 479 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Number Of Units In Package 1	1
Package 1 Length 12.7 cm  Package 1 Weight 479 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Package 1 Height	8 cm
Package 1 Weight 479 g  Unit Type Of Package 2 S02  Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Package 1 Width	8.8 cm
Unit Type Of Package 2 S02  Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Package 1 Length	12.7 cm
Number Of Units In Package 2 9  Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Package 1 Weight	479 g
Package 2 Height 15 cm  Package 2 Width 30 cm  Package 2 Length 40 cm	Unit Type Of Package 2	S02
Package 2 Width 30 cm Package 2 Length 40 cm	Number Of Units In Package 2	9
Package 2 Length 40 cm	Package 2 Height	15 cm
	Package 2 Width	30 cm
Package 2 Weight 4.683 kg	Package 2 Length	40 cm
	Package 2 Weight	4.683 kg

### **Contractual warranty**

Warranty 12 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information