# **Product datasheet**

Specifications





## Circuit breaker basic frame, ComPact NSX100S, 100kA at 415VAC 50/60 Hz, 100A, without trip unit, 3 poles

LV429018

① Discontinued

() Discontinued on: Aug 27, 2020

(!) End-of-service on: Dec 25, 2023

### Main

IVIAIII	
Range	ComPact
Range Of Product	ComPact NSX100250
Device Short Name	NSX100S
Product Or Component Type	Basic frame
Device Application	Distribution
Circuit Breaker Name	Compact NSX100S
Number Of Poles	3P
[In] Rated Current	100 A at 40 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category A
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	100 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 120 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 40 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	S 100 kA 415 V AC
Control Type	Toggle
Mounting Mode	Fixed

### Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ics] Rated Service Short-Circuit Breaking Capacity	100 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 120 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 15 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 40 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 65 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 90 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
Mechanical Durability	50000 cycles conforming to IEC 60947-2

Electrical Durability10000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 20000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 30000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 50000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2Mounting SupportBackplateUpside ConnectionFrontDownside ConnectionFrontProtection Pitch35 mmProtection TypeWithout protectionWidth (W)105 mmHeight (H)161 mmDepth (D)86 mm			
Upside Connection Front   Downside Connection Front   Connection Pitch 35 mm   Protection Type Without protection   Width (W) 105 mm   Height (H) 161 mm	Electrical Durability	20000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 30000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2	
Downside Connection Front   Connection Pitch 35 mm   Protection Type Without protection   Width (W) 105 mm   Height (H) 161 mm	Mounting Support	Backplate	
Connection Pitch 35 mm   Protection Type Without protection   Width (W) 105 mm   Height (H) 161 mm	Upside Connection	Front	
Protection Type Without protection   Width (W) 105 mm   Height (H) 161 mm	Downside Connection	Front	
Width (W)     105 mm       Height (H)     161 mm	Connection Pitch	35 mm	
Height (H) 161 mm	Protection Type	Without protection	
	Width (W)	105 mm	
Depth (D) 86 mm	Height (H)	161 mm	
	Depth (D)	86 mm	

## Environment

Standards	EN/IEC 60947-2 UL 508
Product Certifications	UL CSA
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.7 cm
Package 1 Width	11.2 cm
Package 1 Length	19.0 cm
Package 1 Weight	1.45 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	15
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	22.561 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information