

Product datasheet

Specifications



Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 32A, 230V, (21) C13 & (3) C19

AP8653

Overview

Presentation	APC Metered by Outlet with Switching Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and individual outlet power metering. Remote outlet level controls allow power on/off functionality for power recycling to reboot locked-up equipment and to avoid unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, and locking IEC receptacles. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
Lead Time	Usually in Stock

Main

Colour	Black
Pdu Type	Metered outlet
Cord Length	3.00 m
Number Of Cables	1
Provided Equipment	CAN port terminator Installation guide Rack mounting brackets Safety guide Serial configuration cable

Complementary

Input Voltage	200 V 208 V 230 V
Height	182.9 cm
Width	5.6 cm
Output Voltage	230 V
Depth	5.1 cm
Net Weight	8.23 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 32 A 2P + E
Mounting Mode	Rack-mounted
Rack Units	0U

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Usb Compatible	No
Mounting Position	Vertical
Permissible Voltage	220...240 V
Max Line Current	32 A
Input Current Limits	32 A
Load Capacity	7400 VA
Network Frequency	50/60 Hz
Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19

Environment

Product Certifications	VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3
Ambient Air Temperature For Operation	-5...60 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage Altitude	0.00...15240.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203.8 cm
Package 1 Width	16.2 cm
Package 1 Length	11.8 cm
Package 1 Weight	10.5 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Lead Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins