



# Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 11.0kW, 230V, (21) C13 & (3) C19

AP8681

### **Overview**

#### Presentation

APC Metered by Outlet with Switching Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and individual outlet power metering. Remote outlet level controls allow power on/off functionality for power recycling to reboot locked-up equipment and to avoid unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, and locking IEC receptacles. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.

Lead Time

Usually in Stock

Serial configuration cable

#### Main

Colour	Black
Pdu Type	Switched metered outlet
Cord Length	1.83 m
Provided Equipment	CAN port terminator Installation guide Rack mounting brackets Safety guide

Complementary

Input Voltage	400 V 3 phases
Height	182.9 cm
Width	5.6 cm
Output Voltage	230 V
Depth	5.1 cm
Net Weight	8.23 kg
Mounting Location	Side
Mounting Preference	No preference
Input Plug Type	IEC 60309 16 A 3P + N + PE IEC 60309 20 A 3P + N + PE
Mounting Mode	Not rack-mountable
Rack Units	0U
Mounting Position	Vertical

[In] Rated Current	16 A
Max Line Current	16 A
Input Current Limits	16 A
Load Capacity	11000 VA
Network Frequency	50/60 Hz
Total Number Of Outlets	21 IEC 60320 C13 3 IEC 60320 C19

## **Environment**

Product Certifications	cUL listed UL listed VDE
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC part 15 class A ICES-003
Ambient Air Temperature For Operation	-560 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203.8 cm
Package 1 Width	16.2 cm
Package 1 Length	11.7 cm
Package 1 Weight	10.478 kg

## **Contractual warranty**

Warranty 2 years repair or replace



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

## Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Lead Free

Mercury Free

Rohs Exemption Information Y

Yes

## **Certifications & Standards**

Reach Regulation

Eu Rohs Directive

Compliant with Exemptions

Environmental Disclosure

Product Environmental Profile

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

End of Life Information