# **Product datasheet**

Specification





# PM5350 power monitor

METSEPM5350

### Main

Range	PowerLogic
Product Name	PowerLogic PM5350
Device Short Name	PM5350
Product Or Component Type	Power meter

#### Complementary

Complementary	
Power Quality Analysis	total demand distortion
	total harmonic distortion
Device Application	Power monitoring
Type Of Measurement	Current
	Voltage
	Frequency
	Power factor
	Energy
	Phase angle
	Apparent power
	Active power
	Reactive power
Supply Voltage	85265 V AC 4565 Hz
	100300 V DC
Network Frequency	50 Hz
	60 Hz
[In] Rated Current	5 A
	1 A
Type Of Network	1P + N
	3P + N
	3P
Maximum Power Consumption In Va	11.9 VA
Ride-Through Time	100 ms 120 V AC typical
	400 ms 230 V AC typical
	50 ms 125 V DC typical
Display Type	Monochrome graphic LCD
Display Resolution	6 lines
Sampling Rate	32 samples/cycle
Measurement Current	59000 mA
Analogue Input Type	Current 0.059 A (impedance <= 0.3 mOhm)
- · ·	Voltage (impedance 10 MOhm)
Measurement Voltage	35480 V AC 4565 Hz phase to phase
	20277 V AC phase to neutral
Frequency Measurement Range	4570 Hz

Number Of Inputs	4 digital	
Measurement Accuracy	Current +/- 0.3 %  Voltage +/- 0.3 %  Frequency +/- 0.05 %  Power factor +/- 0.005  Active energy +/- 0.5 %  Reactive energy +/- 2 %  Active power +/- 0.5 %  Apparent power +/- 0.5 %  Apparent energy +/- 0.5 %  Reactive power +/- 0.5 %  Reactive power +/- 2 %	
Accuracy Class	Class 0.5S active energy conforming to IEC 62053-22 Class 0.5 active energy conforming to IEC 61557-12 Class 2 reactive energy conforming to IEC 62053-23 Class 2 reactive energy conforming to IEC 61557-12 Class 0.5 power conforming to IEC 61557-12	
Number Of Outputs	2 relay	
Information Displayed	Tariff (4)	
Communication Port Protocol	JBUS Modbus RTU and ASCII at 9.6, 19.2 and 38.4 kbauds	
Communication Port Support	Terminal block: RS485	
Data Recording	Min/max of instantaneous values Alarms	
Connections - Terminals	Voltage circuit: screw terminal block4 Control circuit: screw terminal block2 Current transformer: screw terminal block6 Input/output circuit: screw terminal block6 Relay output: screw terminal block4 Ethernet network: RJ45 connector	
Mounting Mode	Flush-mounted	
Type Of Installation	For indoor use in a stationary panel	
Standards	IEC 61010-1	
Product Certifications	CE CULus	
Width	96 mm	
Depth	44 mm	
Height	96 mm	
Net Weight	0.25 kg	

### **Environment**

Electromagnetic Compatibility	Limitation of voltage changes, voltage fluctuations and flicker in low-voltage conforming to IEC 61000-3-3  Electrostatic discharge conforming to IEC 61000-4-2  Susceptibility to electromagnetic fields conforming to IEC 61000-4-3  Electrical fast transient/burst immunity test conforming to IEC 61000-4-4  1.2/50 µs shock waves immunity test conforming to IEC 61000-4-5  Conducted RF disturbances conforming to IEC 61000-4-6  Immunity to impulse waves conforming to IEC 61000-4-12  Conducted and radiated emissions class A conforming to EN 55011  Limits for harmonic current emissions conforming to IEC 61000-3-2
Overvoltage Category	III
Ip Degree Of Protection	IP30 rear: conforming to IEC 60529 IP54 display: conforming to IEC 60529
Relative Humidity	595 % at 50 °C non-condensing
Pollution Degree	2

Ambient Air Temperature For Operation	-2570 °C meter -2070 °C display -2520 °C (with reduced performance) display
Ambient Air Temperature For Storage	-40…85 °C
Operating Altitude	<= 3000 m

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.200 cm
Package 1 Width	12.500 cm
Package 1 Length	12.700 cm
Package 1 Weight	346.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.829 kg

## **Contractual warranty**

Warranty 12 months

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Environmental Disclosure	Product Environmental Profile
China Rohs Regulation	China RoHS declaration
Eu Rohs Directive	Compliant with Exemptions
Reach Regulation	REACh Declaration