

Product datasheet

Specifications



BCPM power monitoring advanced - 84 solid core 100 A - 19 mm CT spacing

BCPMA084S

! Discontinued

! Discontinued on: Aug 27, 2020

! To be end-of-service on: Dec 31, 2032

Main

Range	PowerLogic
Product Name	PowerLogic BCPM
Product Or Component Type	Multi-circuit energy meter
Device Short Name	BCPMA
Model Type	Advanced
Power Monitoring	Basic instrumentation
Energy Management	Sub billing and cost allocation
Device Application	Sub billing
Power Quality Analysis	voltage sag and swell detection
Type Of Measurement	Voltage Current Frequency Active power Power factor Active energy
[Us] Rated Supply Voltage	90...277 V AC 50/60 Hz +/- 1 %
Network Frequency	50 Hz 60 Hz

Complementary

Current Transformer Input	Solid core CT 100 A84 x
Update Time	1.8 s
Measurement Voltage	90...277 V phase to neutral 150...480 V phase to phase
Measurement Accuracy	Branch current 2 % 0.25...2 A Branch current 1 % 2...100 A Mains current 3 % 1...100 % Mains current 3 % 2...100 % Voltage 1 % 90...277 V
Sampling Rate	256 samples/cycle
Connection Pitch	19 mm
Provided Equipment	84 x current transformer 4 x cables
Communication Port Protocol	Modbus RTU
Communication Port Support	RS485

Communication Of Data	Low-low current alarm Low current alarm Under voltage alarm High current alarm Over voltage alarm High-high current alarm
------------------------------	--

Environment

Mounting Mode	Panel-mounted
Mounting Support	Panel Enclosure
Relative Humidity	0...95 % at 0...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Operating Altitude	3000 m
Standards	ANSI C12.1 EN 61010 IEC 61036 UL 508
Product Certifications	UL
Width	288 mm
Height	146 mm
Net Weight	1.5 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	159 cm
Package 1 Width	248 cm
Package 1 Length	794 cm
Package 1 Weight	4522.73 g
Unit Type Of Package 2	P06
Number Of Units In Package 2	6
Package 2 Height	50 cm
Package 2 Width	80 cm
Package 2 Length	60 cm
Package 2 Weight	35.5 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
