Product datasheet

Specifications





ClimaSys PTC heating resistance 100W 110-250V

NSYCR100WU2

Overview

Lead Time

Usually Ships within 4 Weeks

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Resistance heater
Range Compatibility	Prisma P Prisma G
Power Range	90 W
Input Voltage	

Complementary

Complementary	
Operating Position	Vertical
Ambient Air Temperature For Operation	-4070 °C
Ip Degree Of Protection	IP20
Product Certifications	UL VDE
Material	Body: extruded aluminium
Height	200 mm
Width	85 mm
Depth	65 mm
Condition Of Use	Heaters must be installed with a thermal controller Air sealed enclosure Electrical protection is needed
Fixing Mode	By clips
Mounting Support	35 mm DIN rail

Packing Units

Unit Type Of Package 1	PCE
	FUL
Number Of Units In Package 1	1
Package 1 Height	6.500 cm
Package 1 Width	8.000 cm
Package 1 Length	20.500 cm
Package 1 Weight	544.000 g

Unit Type Of Package 2	S04
Number Of Units In Package 2	16
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	9.472 kg

Contractual warranty

Warranty

12 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations