

# Product datasheet

Specifications



## ZENCelo - 1 x 2.1A USB Charger - Silver Bronze

E8431USB\_SZ

### Main

Product or component type	USB charger
Device presentation	Mechanism
Colour tint	Silver bronze
Number of terminals	2 screw terminals

### Complementary

Device mounting	Flush
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	1 module 46 x 36.7 x 21.7 mm
Fixing mode	Screw
[Ue] rated operational voltage	100/240 V AC 50/60 Hz
Integrated connection type	1 USB port 5 V DC, maximum load current: 2.1 A
Material	Silicone rubber: cover PC (polycarbonate): grid plate PC (polycarbonate): housing
Shape of screw head	Cross
Clamping connection capacity	2.5 mm <sup>2</sup> for stranded cable(s) 2.5 mm <sup>2</sup> for flexible cable(s) 2.5 mm <sup>2</sup> for rigid cable(s) 1.5 mm <sup>2</sup> for stranded cable(s) 1.5 mm <sup>2</sup> for flexible cable(s) 1.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	6 mm
Product compatibility	Power bank Samsung XiaoMi Major smart phone and tablet Apple HTC HW
Height	87 mm
Width	87 mm
Depth	37.1 mm
Embedding depth	27.3 mm
Net weight	0.07773 kg

## Environment

Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
Product certifications	IEC CCC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	83 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	665 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6.68 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)