

Product datasheet

Specifications



ZENcelo - MAP panel 2-base unit with HDMI/USB - false wall - silver bronze

E84MAPHU9_SZ

! Discontinued on: 29 August 2022

! To be end-of-service on: 01 September 2023

! Discontinued

Main

| | |
|---------------------------|-----------------------|
| Range | ZENcelo |
| Product or component type | Multi-services socket |
| Device application | Media device support |
| Colour tint | Silver bronze |

Complementary

| | |
|-------------------------|---|
| Rated current | 2 A at 12 V DC, tolerance +/- 10 % |
| Connections - terminals | Plug in |
| Material | Box: cold-rolled steel Plate: cold-rolled steel Surround: PC Cover: PC |
| Device mounting | Flush 47 mm |
| Mounting support | Mounting box |
| Mounting location | False wall |
| Fixing mode | By 4 screws |
| Height | 64 mm |
| Width | 87 mm |
| Length | 350 mm |
| Connector type | USB SUB-D 15 HDMI 3.5 mm jack RCA |

Environment

| | |
|---------------------------------------|--|
| Ambient air temperature for operation | 0...40 °C operating 0...60 °C storage |
| Relative humidity | 10...90 % (operating) 0...95 % (storage) |
| Operating altitude | 2000 m |
| Standards | CISPR 22 FCC part 15 class A IEC 60950 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 6.44 cm |
| Package 1 Width | 35.76 cm |
| Package 1 Length | 8.6 cm |
| Package 1 Weight | 885.0 g |

Offer Sustainability

| | |
|----------------------------|---|
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| RoHS exemption information | Yes |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Recommended replacement(s)