
Product datasheet

Specifications





empty control station - XAP-M - metal - 8 horizontal openings

XAPM5508

- () Discontinued on: Dec 31, 2021
- (!) End-of-service on: Jun 30, 2022

U To be discontinu

Main

Range Of Product	Harmony XAP						
Product Or Component Type	Die-cast empty control station						
Device Short Name	ХАРМ						
Product Destination	For Ø 22 mm control and signalling units						
Product Front Plate Size	85 x 310 mm						
Usable Depth	74.5 mm						
Number Of Cut-Out	8 cut-outs						
Colour Of Base Of Enclosure	Blue						
Colour Of Cover	Blue						
Material	Aluminium alloy						
Cable Entry	1 hole without blanking plug for cable gland, clamping capacity: 24 mm						
Ip Degree Of Protection	IP65 conforming to IEC 60529						

Complementary

Number Of Vertical Rows	1
Net Weight	0.81 kg

Environment

Protective Treatment	TC			
Ambient Air Temperature For Storage	-4070 °C			
Ambient Air Temperature For Operation	-4070 °C			

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12 cm
Package 1 Width	9 cm
Package 1 Length	31.5 cm
Package 1 Weight	940 g

Contractual warranty

Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

12 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	No need of specific recycling operations					

Product datasheet

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 24 mm/0.94 in. maximum clamping capacity
- (3) 2 x Ø 5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.
- P Usable depth

а		b		с		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
85	3.35	310	12.20	77	3.03	55	2.17	295	11.61	74.5	2.93

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions



b1 Vertical interaxis: 30 mm/1.18 in.